






O.P. = OPERATING POINT
P.T. = PRE-TRAVEL



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=± 0.4
X.XX=± 0.25
3. RATING: 0.4VA @ 20 VDC OR VAC MAX.
- ▲ 4. CONTACTS: GOLD
- ▲ 5. OPERATING FORCE: 100 ± 30 GRAMS
6. OPERATING TEMP: -25°C TO 85°C
7. ELECTRICAL LIFE: 50,000 CYCLES MIN.
8. MECHANICAL LIFE: 1,000,000 CYCLES TYP.
9. INSULATION RESISTANCE: 100 MEGA-OHMS MIN.
10. DIELECTRIC STRENGTH: 1500VAC 1 MINUTE (INITIAL VALUE)
11. CONTACT RESISTANCE: 100 MILLI -OHMS MAX.
12. ▲ DENOTES CRITICAL PARAMETER.



REV	ECO NO	DESCRIPTION	DATE	BY	 OBJECT ID 000021100				
B	ECO-100844	REMOVE VDE RATING AND LOGO	05/03/22	JS					
					TITLE LS085R105F100C1A				
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE 3:2	DATE 9/10/2015	DR MW	DWG Q950116	REV B