





DO NOT SCALE DRAWING WORK TO FIGURES





MOUNTING HOLE

PANEL THICKNESS
(SNAP - IN BRACKET)
.030 MIN ---- .187 MAX
.76 4.75



$\pm .003$
.250 X .031
6.35 .78



CIRCUIT

LET	REVISIONS	DATE
01	RCV-	7-31-20

RATING

15A 24V

SWITCH FUNCTION

POS 1	POS 2	POS 3
ON	NONE	ON
2 TO 3		2 TO 1
5 TO 6		5 TO 4

NOTES:

- BRACKET AND ROCKER ARE BLACK NYLON
- LOCK BUTTON IS RED LOCKS IN UP POSITION
- LENS COLOR IS WHITE
- LAMP IS INDEPENDENT 24 VOLT SUPERBRIGHT RED LED
- PANEL SEAL

DIMENSIONS SUBJECT TO CHANGE WITHOUT NOTICE

FINISH

CARLINGSWITCH, INC.
PLAINVILLE, CT

PROPRIETARY NOTE:

NOTICE TO ALL PERSONS RECEIVING THIS DRAWING. THIS DOCUMENT IS THE PROPERTY OF CARLINGSWITCH, INC. AND IS NOT TO BE DISCLOSED, REPRODUCED IN WHOLE OR IN PART OR USED FOR MANUFACTURING PURPOSES BY ANYONE WITHOUT THE CONSENT OF CARLINGSWITCH, INC.

UNSPECIFIED TOLERANCES

X.XXX $\pm .015$

PROJECTIONS



DIMENSIONS
IN [mm]

TOOL NO.

REV

DR BY

DATE

CHK BY

DATE

APPD BY

DATE

TITLE

"V" SERIES ROCKER

SIZE

B

DWG NO.

VDB2HWVC-A8D00-0

REV.

01

USED ON

SCALE:

FULL

SHT

1

OF

1