


REV	ECN NO	REVISIONS	DRN	CKD	APP	DATE
A		NEW RELEASE	AJF	KLJ	NO	2-25-11

RoHS COMPLIANT 521-8268F
Part Numbers with the "F" suffix ending are RoHS Compliant.
Packaging is marked with "RoHS Compliant" label or equivalent
markings. Parts can be wave soldered, dip soldered or hand
soldered using typical lead-free soldering process with max
260°C temp. for 5 sec.




OPERATING CHARACTERISTICS AT 25°C AMBIENT					
LED CHARACTERISTICS	MIN.	TYP.	MAX.	UNITS	TEST CONDITIONS
LUMINOUS INTENSITY	5500	9300	12000	mcd	I _F = 20 mA
FORWARD VOLTAGE	2.7	3.3	3.6	V	I _F = 20 mA
REVERSE CURRENT	—	—	10	μA	V _R = 5 V
VIEWING ANGLE	—	25	—	DEGREE	
CHROMATICITY COORDINATES	X	—	0.30	—	I _F = 20 mA SEE HUE SPEC. TABLE
	Y	—	0.30	—	

ABSOLUTE MAXIMUM RATINGS AT 25°C AMBIENT	VALUE	UNITS
POWER DISSIPATION	120	mW
PEAK FORWARD CURRENT (1/10 DUTY CYCLE, 0.1ms PULSE WIDTH)	100	mA
CONTINUOUS FORWARD CURRENT	30	mA
LINEAR DERATING FROM 30°C	0.5	mA/°C
REVERSE VOLTAGE	5	V
LEAD SOLDERING TEMPERATURE (.080" [2,0mm] FROM BODY) FOR 5 SEC.	260	°C
OPERATING TEMPERATURE	-30 TO +80	°C
STORAGE TEMPERATURE	-40 TO +100	°C

HUE SPEC. TABLE						
HUE RANK	CHROMATICITY COORDINATES LIMITS I _F =20mA					
A1	X	0.2500	0.2700	0.2700	0.2500	
	Y	0.2175	0.2455	0.2780	0.2500	
A2	X	0.2500	0.2700	0.2700	0.2500	
	Y	0.1850	0.2130	0.2455	0.2175	
B1	X	0.2700	0.2900	0.2900	0.2700	
	Y	0.2455	0.2735	0.3060	0.2785	
B2	X	0.2700	0.2900	0.2900	0.2700	
	Y	0.2130	0.2410	0.2735	0.2455	
C1	X	0.2900	0.3100	0.3100	0.2900	
	Y	0.2735	0.3030	0.3355	0.3060	
C2	X	0.2900	0.3100	0.3100	0.2900	
	Y	0.2410	0.2705	0.3030	0.2735	
COLOR COORDINATES MEASUREMENT ALLOWANCE IS ±0.01						

- NOTES:
- DIALIGHT PART NUMBER: 521-8268F.
 - LED COLOR: InGaN WHITE.
 - EPOXY COLOR: WATER CLEAR.
 - LEAD SPACING MEASURED NEAR EPOXY PACKAGE.
 - PIN NUMBERS ARE FOR REFERENCE ONLY, DESIGNATION NON-EXISTENT ON PART.
 - THIS ASSEMBLY CONTAINS ELECTROSTATIC DISCHARGE SENSITIVE DEVICES (ESDS). MAINTAIN ALL PRECAUTIONARY MEASURES DURING ASSEMBLY, HANDLING AND STORAGE IN ACCORDANCE WITH IPC-A-610.



THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT.		
SCALE: 8.000	DRAWING NUMBER	REV
ALL DIM'S IN: INCHES (MM)	C-17906	A
TOLERANCES: UNLESS OTHERWISE SPECIFIED	TITLE Ø 3mm WHITE LED, WATER CLEAR	
FRACTIONS: ±1/64	MATERIAL -	
DECIMALS (.XXX): ±.010	Dialight 1501 ROUTE 34 SOUTH FARMINGDALE, NJ 07727	
ANGLES: ±1°	FSCM 83330	
FINISH: -	SHEET 1 OF 1 FAMILY TABLE:	