

**CSL1,6R18-16 SN I3,5****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Similar to illustration

**For a reliable contact - CB/CS crimp contact.**

The combination of RSV housings and Weidmüller's crimp contacts enable custom adaptations to the specific requirements of your applications.

The following product options are available depending on the system:

- Safe centring of the contacts using the three-segment pin tips
- High contact reliability using four defined contact points
- Locking clasp in the cantilever spring for a secure mount of the contacts in the housing
- Pin contacts with two lengths to implement leading-pin contacts
- Up to 100 plugging cycles (tin version)
- Up to 500 plugging cycles (gold version)

The appropriate high-quality tools from Weidmüller guarantee professional processing.

**General ordering data**

|              |                                                                                                                         |
|--------------|-------------------------------------------------------------------------------------------------------------------------|
| Version      | PCB plug-in connector, Crimp contact, Reel packaged, Pin &dash; long, tinned, Max. clamping range : 1.5 mm <sup>2</sup> |
| Order No.    | <a href="#">1582360000</a>                                                                                              |
| Type         | CSL1,6R18-16 SN I3,5                                                                                                    |
| GTIN (EAN)   | 4008190063214                                                                                                           |
| Qty.         | 4,000 pc(s).                                                                                                            |
| Product data |                                                                                                                         |
| Packaging    | Box                                                                                                                     |

## CSL1,6R18-16 SN I3,5

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight 0.75 g

## System Parameters

|                        |                  |                  |      |
|------------------------|------------------|------------------|------|
| Wire connection method | Crimp connection | Number of poles  | 1    |
| Volume resistance      | 3.30 mΩ          | Stripping length | 4 mm |

## Material data

|                                       |        |                                       |        |
|---------------------------------------|--------|---------------------------------------|--------|
| Contact material                      | CuZn   | Contact surface                       | tinned |
| Storage temperature, min.             | -40 °C | Storage temperature, max.             | 70 °C  |
| Operating temperature, min.           | -50 °C | Operating temperature, max.           | 100 °C |
| Temperature range, installation, min. | -25 °C | Temperature range, installation, max. | 100 °C |

## Conductors suitable for connection

|                                         |                      |                                         |                     |
|-----------------------------------------|----------------------|-----------------------------------------|---------------------|
| Clamping range, min.                    | 0.75 mm <sup>2</sup> | Clamping range, max.                    | 1.5 mm <sup>2</sup> |
| Wire connection cross section AWG, min. | AWG 18               | Wire connection cross section AWG, max. | AWG 16              |
| Flexible, min. H05(07) V-K              | 0.75 mm <sup>2</sup> | Flexible, max. H05(07) V-K              | 1.5 mm <sup>2</sup> |
| Outer diameter of insulation, min.      | 2 mm                 | Outer diameter of insulation, max.      | 3.5 mm              |

## Rated data acc. to IEC

tested acc. to standard IEC 60664-1, IEC 61984

## Packing

|           |        |            |        |
|-----------|--------|------------|--------|
| Packaging | Box    | VPE length | 600 mm |
| VPE width | 580 mm | VPE height | 60 mm  |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002943    | ETIM 7.0    | EC002943    |
| ETIM 8.0    | EC002943    | ECLASS 9.0  | 27-44-04-92 |
| ECLASS 9.1  | 27-44-04-92 | ECLASS 10.0 | 27-44-04-92 |
| ECLASS 11.0 | 27-46-04-03 | ECLASS 12.0 | 27-46-04-03 |

## Important note

IPC conformity Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

Notes

- The long pins can be used with the standard pins as leading contacts.
- Long term storage of the product with average temperature of 50 °C and average humidity 70%, 36 months

## Approvals

ROHS Conform

## CSL1,6R18-16 SN I3,5

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Approval/Certificate/Document of  
Conformity

[Declaration of the Manufacturer](#)

Engineering Data

[CAD data – STEP](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

[MB DEVICE MANUF. EN](#)  
[FL 72H SAMPLE SER EN](#)  
[PO OMNIMATE EN](#)  
[PO OMNIMATE EN](#)

## CSL1,6R18-16 SN I3,5

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

## Drawings



## Dimensional drawing

