








P.C. MOUNTING



O.P. (MM)	P.T. (MM)
20.7 ± 1.5	5.5 MAX

O.P. = OPERATING POINT
P.T. = PRE-TRAVEL



CIRCUIT: SPDT

NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- RATING: 15A @ 125/250 VAC-UL, CUL
- ▲ OPERATING FORCE: 120 ± 40 gf
- OPERATING TEMP: -25°C to 85°C
- ELECTRICAL LIFE: 50,000 CYCLES MIN.
- MECHANICAL LIFE: 1,000,000 CYCLES TYP.
- INSULATION RESISTANCE: 100 MEGA-OHMS MIN @ 500VDC
- DIELECTRIC STRENGTH: 1500VAC 1 MINUTE (INITIAL VALUE)
- CONTACT RESISTANCE: 100 MILLI -OHMS MAX.
- ▲ DENOTES CRITICAL PARAMETER

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
C	ECO-102153	P.T 5.5 MAX WAS 2.5	08/15/23	JS	TITLE LS0851506F120V2A				000021106
					SCALE	DATE	DR	DWG	REV
					3:2	8/24/2018	MW	Q950122	C

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED