




REV. 0

DCO 16835


COIL: @ 25°C
 RESISTANCE 27 OHMS ±10%
 NOMINAL VOLTAGE 5.0 VDC
 MUST OPERATE 2.7 VDC
 MUST RELEASE .29 VDC

ENVIRONMENT:

VIBRATION 10 CPS TO 2000 CPS @ 20 g's
 SHOCK 100 g's 6 MS. DURATION
 TEMPERATURE -55 °C TO +85 °C

NOTES: OPERATE & RELEASE 4 MS MAX
 CONTACT BOUNCE 2 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 5 A
 28 VDC RESISTIVE 100,000 OPERATIONS

DR. PBB 2/22/01 CK. TLG 02-22-01

CII Technologies
 advanced control electronic solutions

CUST. CII STD

CUST. NO. REV.

HFW5A RELAY

HFW5A1230L00