

NOTES:

1. MATERIALS AND FINISHES:

BODY

- BRASS, NICKEL PLATING

CONTACT

- BERYLLIUM COPPER, SILVER PLATING

INSULATOR

- PTFE, NATURAL

2. ELECTRICAL:

A. IMPEDANCE: 50 OHM

B. FREQUENCY RANGE: DC-11 GHz

C. DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS, MIN.

3. MECHANICAL:

A. DURABILITY: 500 CYCLES MIN.

B. TEMPERATURE RANGE: -65°C TO +165°C

4. PACKAGING:

A. QUANTITY: SINGLE PACK

B. MARKING: PACKAGING TO BE MARKED

"AMPHENOL RF, 000-79825, AND DATE CODE"

THIRD ANGLE PROJ.

REV

DESCRIPTION

DATE

ECN

APPR

A

RELEASE TO MFG.

18-Apr-63

8403

--

U

REDRAWN, ADDED SHEET 2

19-Feb-20

14427

EH

SCALE 2.000

CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES ± 0.05mm ±0.1mm ±0.2mm ± 0.3mm ±1° NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	MATERIAL	DRAWN	DATE	TITLE		Amphenol RF	
	NOTE 1	E. HILL	27-Jan-20				
	REFERENCE	ENGINEER	DATE				
	EAR# ---	E. HILL	27-Jan-20	SCALE: 4.0:1.0		DRAWING NO. 000-79825	
	REF: ---	APPROVED	DATE				
CONFIGURATION LEVEL: In Work		M. HOYACK	19-Feb-20	SHEET 2 OF 2		ITEM NO. 000-79825	
FINISH		CAD FILE		DWG SIZE		PART NO. 000-79825	
				B			
				REV			
				U			