






NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 12VDC, 50mA
- ▲ 5. OPERATING FORCE: 65 ± 20 GRAMS
6. TRAVEL: 0.25mm +0.2/-0.1
7. CONTACT RESISTANCE: 100 mΩ MAX. (INITIAL)
8. MECHANICAL/ELECTRICAL LIFE 5,000,000 CYCLES MIN.
- ▲ 9. SILVER CONTACTS
- ▲ 10. OPERATING TEMPERATURE: -20°C TO 70°C
11. ▲ DENOTES CRITICAL PARAMETER
12. 2002/95/EC (ROHS) COMPLIANT
13. INSULATION RESISTANCE: 100MΩ MIN
14. DIELECTRIC STRENGTH: 250 VAC



B	21401	CORRECT LIFE CYCLES	3/10/14	EBP
A	21359	INITIAL RELEASE	1/24/14	EBP
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE LL3301NF065QJ

SCALE

DATE

1/24/2014

DR

EBP

DWG

P090010

REV

B