

## K78MXX-2000R3

Medical  
electric  
equipmentPower  
Factor  
Correction

World wide

Safety  
Approvals

EMI

Inrush  
current  
limiting

OCP




OVP

Remote  
ON/OFFParallel  
Operation

1U

## K-series



## ■ Feature

DC-DC converters  
Ideal for semiconductor,  
analytical, medical,  
and detector applications  
Accuracy, reliability and stability  
are critical for high voltage DC-DC  
applications. manufacturers, with  
over 20 years of experience providing  
accurate and reliable compact solutions.  
applications – allowing us to maximize  
functionality in a compact environment

## ■ Safety agency approval

ENI 55032:2015/A1:2020  
EN IEC 62368-1:2020+A11:2020  
IEC 62321-1:2013 IEC 62321-2:2021 IEC 62321-3-1:2013,

## ■ Up to 5-year warranty (Refer to Instruction Manual)

## ■ CE FCC marking

Low Voltage Directive  
RoHS Directive

## ■ ROHS REACH marking

Electrical Equipment Safety Regulations  
RoHS Regulations

## ■ EMI

- PCA300F, PCA600F  
Complies with FCC-B, CISPR32-B, EN55011-B, EN55032-B, VCCI-B
- PCA1000F, PCA1500F  
Complies with FCC-A, CISPR32-A, EN55011-A, EN55032-A, VCCI-A

## ■ EMS Compliance : EN61204-3, EN61000-6-2

IEC60601-1-2 (2014), EN60601-1-2 (2015)

EN61000-4-2  
EN61000-4-3  
EN61000-4-4  
EN61000-4-5  
EN61000-4-6  
EN61000-4-8  
EN61000-4-11

## Features

- Efficiency up to 97%, no heatsinks required
- Pin-out compatible with LM78XX linears
- Low profile (L/W/H=11.6 x 10.15 x 7.6mm)
- Short circuit protection, thermal shutdown
- Operating ambient temperature range: -40°C to +85°C

## Description

The K78XXM-1000R3-Series are high efficiency switching regulators and ideal substitutes for LM78xx series three-terminal linear regulators. The converters feature high efficiency, low loss, short circuit protection, and there is no need for a heat sink.

These products are widely used in applications such as industrial control, instrumentation and electric power.

## Technical Specification

All specifications are typical at nominal input, full load and 25°C unless otherwise stated.

| Model Number  | Input Voltage Range                     | Output Voltage (V) | Output Current (mA)      |            | Full Load Efficiency(%) Typ.<br>Vin Min./ Vin Max. | Capacitive Load(uF) Max. |
|---------------|---|--------------------|--------------------------|------------|--|--------------------------|
|               |   |                    | Min. Load <sup>(1)</sup> | Full. Load |  |                          |
| K7803M-1000R3 | 4.75-36V <sup>(*)</sup><br>Nominal: 24V | 3.3                | 0                        | 1000       | 94/84  | 1000                     |
| K7805M-1000R3 | 6.5-36V<br>Nominal: 24V                 | 5                  | 0                        | 1000       | 96/88  | 1000                     |
| K7812M-1000R3 | 15-36V<br>Nominal: 24V                  | 12                 | 0                        | 1000       | 97/93  | 330                      |
| K7815M-1000R3 | 18-36V<br>Nominal: 24V                  | 15                 | 0                        | 1000       | 97/94  | 330                      |

## Input Specifications

|                        |                                     |                        |
|------------------------|-------------------------------------|------------------------|
| Input voltage          | 24V nominal input                   | 4.75V Min.<br>36V max. |
| Input filter           |                                     | Capacitor              |
| Input Reverse Polarity | See Positive to Negative Converter, |                        |
| No Load Input Current  |                                     | 30mA max.              |

Hot swap is not supported

## Environmental Specifications

|                               |                |                   |
|-------------------------------|----------------|-------------------|
| Operating ambient temperature | with derating  | -40°C to +85°C    |
| Storage temperature range     |                | -55°C to +125°C   |
| Maximum case temperature      |                | +100°C            |
| Operating humidity            | Non-condensing | 95% RH max.       |
| Temperature coefficient       |                | ±0.015% / °C Typ. |
| RoHS Compliant                |                | RoHS 2.0          |

## Output Specifications

|   |                                 |                               |
|---|---------------------------------|-------------------------------|
| Voltage accuracy                                  | At 100% load                    | ±2.0% Typ<br>±4.0% max.       |
| Line regulation                                   | Vin=min. to max. Vout=100% load | ±0.2% Typ<br>±0.4% max.       |
| Load Regulation                                   | Vin=nom. Vout=10 -100% load     | ±0.4% Typ<br>±0.8% max.       |
| Ripple and Noise (20MHz Bandwidth) <sup>(4)</sup> | Vin=nom. Vout=100% load         | 50mVp-p Typ.<br>100mVp-p max. |

|                                |           |                          |
|--------------------------------|-----------|--------------------------|
| Over Current Protection(OCP)   | 100%=1.0A | 300~500%                 |
| Short Circuit Protection (SCP) |           | Continuous, autorecovery |

## General Specifications


|                       |                                       |                         |
|-----------------------|---------------------------------------|-------------------------|
| Efficiency            |                                       | See table               |
| Switching frequency   | Pulse width modulation(PWM), Vin=nom. | 410KHz                  |
| Dynamic load response | 75-100-75% load step                  | <250uS Typ              |
| MTBF                  | According to MIL-HDBK-217F,G.B. +25°C | 2.0×10 <sup>7</sup> Hrs |
| Safety <sup>(5)</sup> | IEC/EN60950-1,2nd Edition,EN55032     | meet                    |

## Physical Specifications


|            |  |  |
|------------|--|--|
| Dimensions |  | 0.45 × 0.41 × 0.3 Inch<br>(11.6 × 10.4 × 7.6 mm) |
| Weight     |  | 2.0g (0.07oz) typ.                               |

| EMC Compliance  | Condition                | Standard/Criterion                 |
|---|--------------------------|------------------------------------|
| Electromagnetic compatibility of multimedia equipment-Emission requirements | with external components | EN55032,Class A<br>EN55032,Class B |
| ESD Electrostatic discharge immunity test                                   | Air ±8kV,Contact ±4kV    | EN61000-4-2,Criteria B             |
| Radiated,radio-frequency,electromagnetic field immunity test                | 10V/m                    | EN61000-4-3,Criteria A             |




Power Derating Curve



Efficiency Curve

**Note****Ambient Temperature (°C)**

1. Io below this value will not damage these converters, however, they may not meet all listed specifications.
2. Typical value, tested at nominal input and full load.
3. Operation under no load will not harm the converter, but specifications may not be met. A minimum load of 10mA is recommended.
4. With light loads at or below 10%, Ripple & Noise for 3.3V/5V output parts increases to 150mVp-p max, and for other output parts to 2%Vo max.
5. Input Back Ripple Current is tested and specified over a 5 Hz to 20 MHz bandwidth.  
Input filtering is Cin=100 uF\*2, Cbus=1000 uF, Lbus=1 uH. All caps are low ESR. (see page 6 **EMI Filter**)

**Output Load****Mechanical Dimensions**


| Pin Assignment |        |
|----------------|--------|
| Pin            | Define |
| 1              | Vin    |
| 2              | GND    |
| 3              | Vout   |

Unit: mm

Tolerance: XX.X=±0.5, XX.XX=±0.25


## Test Configurations

All specifications are typical at nominal input, full load and 25°C unless otherwise stated.




- ⊙DC Power Supply: It offers a wide voltage and current range precisely.
- ⊙Current meter (A): Accuracy → 200μA ~ 200mA 4 ranges  $\pm(0.2\% \text{ rdg} + 2 \text{ digits})$   
2000mA ~ 20A 2 ranges  $\pm(0.3\% \text{ rdg} + 2 \text{ digits})$ .
- ⊙Voltage meter (V): Accuracy →  $\pm(0.03\% \text{ rdg} + 4 \text{ digits})$ .
- ⊙Load: At full load.
- ⊙Wires: The resistance of the wires must be small.

1. **Ripple and Noise**: as shown below. The bandwidth is 0-20MHz.




Output Ripple&Noise measurement test circuit: as shown below.



Co: usually 10μF to 47μF use low-ESR ceramic.


2. **Application circuit**: as shown below. C1=22μF/50V, C2=47μF/16V Low ESR.



## EMI Filter


Input filter components are used to meet emissions requirement for the module.

These components should be mounted as close as possible to the module; and all leads should be minimized to decrease noise.



$C_{IN} = 2 \times 100\mu F$ ,  $ESR < 700m\Omega$  @ 100kHz  
 $C_{BUS} = 1000\mu F$ ,  $ESR < 100m\Omega$  @ 100kHz  
 $C_{BUS} = 1\mu F$

## Positive to Negative Converter



C1 and C2 are required and should be fitted close to the converter pins.

Maximum capacitive load including C2 is 100uF