

CMOS 4-bit Single Chip Microcontroller

- High Performance 4-bit Core CPU S1C63000
- Flash EEPROM 16K x 13bit / 4K x bit
- Segment LCD Driver (Max:56SEG x 8COM)
- R/F Converter to Measure Temperature and Humidity
- Low Current Consumption
- Low Voltage Operation

■ DESCRIPTIONS

The S1C6F016 is a microcontroller features low voltage operations and low current consumption. It consists of a 4-bit core CPU S1C63000 as the core CPU, Flash EEPROM (16K words x 13 bits), RAM (2K words x 4 bits), supply voltage detection (SVD) circuit, serial interface, timers, sound generator, and integer multiplier. It also incorporates a segment LCD controller/driver that can drive a maximum 56-segment x 8-common LCD panel, and an R/F converter that can measure temperature and humidity using sensors such as a thermistor.

The S1C6F016 is suitable for battery driven clocks and watches with temperature and humidity measurement functions.


■ FEATURES

● CPU	4-bit CMOS core CPU S1C63000
● OSC1 oscillation circuit	32.768kHz (Typ.) crystal oscillation circuit
● OSC3 oscillation circuit	4.2MHz (Max.) ceramic oscillation circuit
	1.8MHz (Typ.) CR oscillation circuit (external R), or
	500kHz (Typ.) CR oscillation circuit (built-in R) (*1)
● Instruction set	47 types of basic instructions (411 instructions with all), 8 types of addressing modes
● Instruction execution time	During operation at 32.768kHz: 61μsec 122μsec 183μsec During operation at 4MHz: 0.5μsec 1μsec 1.3μsec
● Flash EEPROM capacity	Code ROM: 16,384 words x 13 bits Data ROM: 4,096 words x 4 bits
● RAM capacity	Data memory: 2,048 words x 4 bits Display memory: 448 bits
● LCD driver	56 segments (Max., *1) x 3 to 8 commons (*2)
● I/O ports	24 bits
● Serial interface	1 port (8-bit clock synchronous system with SPI supported)
● Time base counters	Clock timer 1/1000-second stopwatch timer with direct key input function
● Programmable timer	16-bit timer x 2 channels Each 16-bit timer is configurable to two 8-bit timer channels (*2)
● Watchdog timer	Built-in
● Sound generator	With envelope and 1-shot output functions
● R/F converter	2 channels, CR oscillation type R/F converter with 20-bit counters, supports resistive humidity sensors
● Integer Multiplier	8-bit accumulator x 1 channel Multiplication: 8 bits x 8 bits → 16-bit product Division: 16 bits ÷ 8 bits → 8-bit quotient and 8-bit remainder
● Supply voltage detection (SVD) circuit	Programmable 16 detection voltage levels (*2)
● External interrupt	Key input 8 systems
● Internal interrupt	Watchdog timer (NMI) 1 systems
	Clock timer 8 systems
	Stopwatch timer 4 systems
	Programmable timer 8 systems
	Serial interface 1 systems
	R/F converter 3 systems
● Power supply voltage	1.8 to 3.6V (for normal operation), 2.7 to 3.6V (for Flash programming) (*1)
● Operation temperature range	-20 to 70°C
● Current consumption (Typ.)	During SLEEP (32kHz) 0.7μA During HALT (32kHz) 2μA During running (32kHz) 9μA During running (4MHz) 950μA
● Shipment form	QFP15-100pin or die form

*1: Can be selected with mask option. *2: Can be selected with software.

S1C6F016

■ BLOCK DIAGRAM



NOTICE:

No part of this material may be reproduced or duplicated in any form or by any means without the written permission of Seiko Epson. Seiko Epson reserves the right to make changes to this material without notice. Seiko Epson does not assume any liability of any kind arising out of any inaccuracies contained in this material or due to its application or use in any product or circuit and, further, there is no representation that this material is applicable to products requiring high level reliability, such as, medical products. Moreover, no license to any intellectual property rights is granted by implication or otherwise, and there is no representation or warranty that anything made in accordance with this material will be free from any patent or copyright infringement of a third party. This material or portions thereof may contain technology or the subject relating to strategic products under the control of the Foreign Exchange and Foreign Trade Law of Japan and may require an export license from the Ministry of Economy, Trade and Industry or other approval from another government agency.

All brands or product names mentioned herein are trademarks and/or registered trademarks of their respective companies.

©Seiko Epson Corporation 2010, All rights reserved

SEIKO EPSON CORPORATION

SEMICONDUCTOR OPERATIONS DIVISION

EPSON semiconductor website

http://www.epson.jp/device/semicon_e/

IC Sales Department
IC International Sales Group
421-8 Hino, Hino-shi, Tokyo 191-8501, JAPAN
Phone: +81-42-587-5814 FAX: +81-42-587-5117

Document code: 411904700
First issue Mar, 2010 in Japan