

NOTES:


- ① MAT'L: COPPER (STOCK TKN. $\frac{.031}{.79}$)
PLATING: ELECTRO TIN (.0003 MIN)
- ② TIN-PLATED BRASS FUNNEL FERRULE
- ③ NYLON INSULATION (COLOR CODED BLUE)

STUD SIZES: ($\pm .005$)

02 = .094
04 = .119
06 = .146
08 = .173
10 = .198
14 = .265
56 = .328
38 = .390

"UL" LISTING #E32244
"CSA" LISTING #18689

WIRE SIZE: 16-14 AWG
1.0-2.5 MM²



ALL DIMENSIONS = $\frac{\text{INCHES}}{\text{MM}}$

(MWID) = DENOTES MAXIMUM WIRE INSULATION DIAMETER

PART
NUMBER

"W"
 $\pm .010$

"C"
MIN.

"L"
MAX.

AVAILABLE
STUD SIZES

B-523-

$\frac{.250}{6.35}$

$\frac{.209}{5.31}$

$\frac{.833}{21.16}$

04,06,08

DIMENSIONAL TOLERANCES
UNLESS OTHERWISE SPECIFIED

REFERENCE

SCALE: NTS

DATE

TITLE:

DRWN. BY: *JS*

11-12-84

CHKD. BY: *62*

11-30-84

APPRD. BY:

RING TONGUE
TERMINAL
AVIKRIMP
500-SERIES

ETCmolex
INCORPORATED

DWG.
NO.

A

CUSTOMER
DWG