




COIL: @ 25°C

RESISTANCE 675 OHMS $\pm$ 10%

NOMINAL VOLTAGE 26.5 VDC

MUST OPERATE 13.0 VDC

MUST RELEASE 10.1 VDC MAX, 2.3 VDC MIN.

ENVIRONMENT:


VIBRATION 10 CPS TO 2000 CPS @ 20 g's

SHOCK 100 g's 6 $\pm$ 1 MS. DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE & RELEASE TIME 6 MS MAX.
CONTACT BOUNCE 1 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: 2 AMPS 28 VDC
RESISTIVE 100,000 OPERATIONS

DR. R.B. 2/9/95 CK. 2/9/95

COMMUNICATIONS
INSTRUMENTS, INC.

CUST. OPL
 CUST. NO. M5757/10-040

TYPE "FW" RELAY

FW1220G06