

CIRCUIT: DPDT
CONTACT CONFIGURATION

SWITCH FUNCTION			
POS. 1	POS. 2	POS. 3	
(DN)	DIFF	(DN)	
2-3,5-6	OPEN	2-1,5-4	



NOTES:

(>)=Momentary



1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.XX=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. RATING: 0.4VA @20V AC or DC max.
5. FIXED TERM. & MOVING CONTACT:

Copper Alloy W/Gold plate over
Nickel plate.

6. ELECTRIC LIFE: 40,000 make-and-break cycles
at full load.
7. INSULATION RESISTANCE: 1,000 Mega-ohm min.
8. DIELECTRIC STRENGTH: 1,000 V RMS @sea level.
9. OPERATING TEMP.: -30°C to 85°C



BOTTOM VIEW



TITLE			
100A WDP4 T1 B1 M1 R E (GOLD CONTACTS)			
RELEASED			
9/20/02			
CB			
DESCRIPTION			
DATE			
CHKD			
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
SCALE			
2:1			
DATE			
9/20/02			
DR			
CB			
DWG			
T102283			
REV			
A			

E-SWITCH®