





▲ SCHEMATIC
 DPST
 OFF - (ON)
 MOMENTARY



NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- ELECTRICAL LIFE: 6,000 [cURus]
- CONTACT RESISTANCE: 20 m Ω MAX. INITIAL
- INSULATION RESISTANCE: 100 M Ω AT 500VDC
- OPERATING TEMPERATURE: -20°C to +65°C
- CONTACT RATING: 16A, 125VAC-250VAC, [cURus]
- DIELECTRIC STRENGTH: 1000V FOR 1 MINUTE
- ACTUATION FORCE: 1000 $\pm$ 300 gf
- TRAVEL: TO LOCK POSITION: 3.0mm
FULL TRAVEL: 5.0mm
- ▲ DENOTES CRITICAL PARAMETER

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
B	ECO-100639	update rating	01/10/22	MW	TITLE PA55EJ				100118405
					SCALE	DATE	DR	DWG	REV
					3:2	9/7/2021	MW	14-PA55EJ	B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
 E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED