

T-1 $\frac{3}{4}$ (5mm) Solid State Lamps

LTL-307R/307RE	Red
LTL-307P/307PE	Bright Red
LTL-307E/307EE	High Efficiency Red
LTL-307G/307GE	Green
LTL-307Y/307YE	Yellow

Feature

- High Intensity.
- Popular T-1 $\frac{3}{4}$ diameter package.
- Selected minimum intensities.
- Wide viewing angle.
- General purpose leads.
- Reliable and rugged.

Description

The Red source color devices are made with Gallium Arsenide Phosphide on Gallium Arsenide Red Light Emitting Diode.


The Bright Red source color devices are made with Gallium Phosphide on Gallium Phosphide Red Light Emitting Diode.

The High Efficiency Red and Orange source color devices are made with Gallium Arsenide Phosphide on Gallium Phosphide Orange Light Emitting Diode.

The Green source color devices are made with Gallium Phosphide on Gallium Phosphide Green Light Emitting Diode.

The Yellow source color devices are made with Gallium Arsenide Phosphide on Gallium Phosphide Yellow Light Emitting Diode.

Package Dimensions



Notes:

1. All dimensions are in millimeters (inches).
2. Tolerance is $\pm 0.25\text{mm}$ (0.10") unless otherwise noted.
3. Protruded resin under flange is 1.0mm (.04") max.
4. Lead spacing is measured where the leads emerge from the package.
5. Specifications are subject to change without notice.

Devices

Part No. LTL-	Lens		Source Color
	Color	Diffusion	
307R 307RE	Red	Diffused Transparent	Red
307P 307PE	Red	Diffused Transparent	Bright Red
307E 307EE	Red	Diffused Transparent	Hi. Eff. Red
307G 307GE	Green	Diffused Transparent	Green
307Y 307YE	Yellow	Diffused Transparent	Yellow

Absolute Maximum Ratings at Ta=25 °C

Parameter	Red	Bright Red	Green	Yellow	Hi. Eff. Red Orange	Unit
Power Dissipation	80	40	100	60	100	mW
Peak Forward Current (1/10 Duty Cycle, 0.1ms Pulse Width)	200	60	120	80	120	mA
Continuous Forward Current	40	15	30	20	30	mA
Derating Linear From 50 °C	0.5	0.2	0.4	0.25	0.4	mA/ °C
Reverse Voltage	5	5	5	5	5	V
Operating Temperature Range	-55 °C to +100 °C					
Storage Temperature Range	-55 °C to +100 °C					
Lead Soldering Temperature [1.6mm (.063") From Body]	260 °C for 5 Seconds					




Fig.1 RELATIVE INTENSITY VS. WAVELENGTH

Electrical /Optical Characteristics and Curves at Ta=25 °C

Parameter	Symbol	Part No. LTL-	Min.	Typ.	Max.	Unit	Test Condition
Luminous Intensity	I_v	307R 307P 307E 307G 307Y	0.5 1.7 5.6 5.6 8.7	1.7 5.6 19 19 29		mcd	$I_F = 10\text{mA}$ Note 1
Viewing Angle	$2\theta_{1/2}$	307R 307P 307E 307G 307Y		50		deg	Note 2 (Fig.7)
Peak Emission Wavelength	λ_P	307R 307P 307E 307G 307Y		655 697 635 565 585		nm	Measurement @ Peak (Fig.1)
Dominant Wavelength	λ_d	307R 307P 307E 307G 307Y		651 657 621. 569 588		nm	Note 3
Spectral Line Half Width	$\Delta\lambda$	307R 307P 307E 307G 307Y		24 90 40 30 35		nm	
Forward Voltage	V_F	307R 307P 307E 307G 307Y		1.7 2.1 2.0 2.1 2.1	2.0 2.8 2.8 2.8 2.8	V	$I_F = 20\text{mA}$
Reverse Current	I_R	307R 307P 307E 307G 307Y			100	μA	$V_R = 5\text{V}$
Capacitance	C	307R 307P 307E 307G 307Y		30 55 20 35 15		PF	$V_F=0$ $f=1\text{MHZ}$

Notes:

- Luminous intensity is measured with a light sensor and filter combination that approximates the CIE eye-response curve.
- $\theta_{1/2}$ is the off-axis angle at which the luminous intensity is half the axial luminous intensity.
- The dominant wavelength, λ_d is derived from the CIE chromaticity diagram and represents the single wavelength which defines the color of the device.









Electrical /Optical Characteristics and Curves at Ta=25 °C

Parameter	Symbol	Part No. LTL-	Min.	Typ.	Max.	Unit	Test Condition
Luminous Intensity	Iv	307RE 307PE 307EE 307GE 307YE	1.1 2.5 29 19 12.6	3.7 8.7 90 60 40		mcd	If = 10mA Note 1
Viewing Angle	2 θ 1/2	307RE 307PE 307EE 307GE 307YE		40		deg	Note 2 (Fig.15)
Peak Emission Wavelength	λ P	307RE 307PE 307EE 307GE 307YE		655 697 635 565 585		nm	Measurement @ Peak (Fig.1)
Dominant Wavelength	λ d	307RE 307PE 307EE 307GE 307YE		651 657 621. 569 588		nm	Note 3
Spectral Line Half Width	$\Delta \lambda$	307RE 307PE 307EE 307GE 307YE		24 90 40 30 35		nm	
Forward Voltage	V _F	307RE 307PE 307EE 307GE 307YE		1.7 2.1 2.0 2.1 2.1	2.0 2.8 2.8 2.8 2.8	V	If = 20mA
Reverse Current	I _R	307RE 307PE 307EE 307GE 307YE			100	μA	V _R = 5V
Capacitance	C	307RE 307PE 307EE 307GE 307YE		30 55 20 35 15		PF	V _F =0 f=1MHZ

Notes:

1. Luminous intensity is measured with a light sensor and filter combination that approximates the CIE eye-response curve.
2. θ 1/2 is the off-axis angle at which the luminous intensity is half the axial luminous intensity.
3. The dominant wavelength, λ d is derived from the CIE chromaticity diagram and represents the single wavelength which defines the color of the device.

Typical Electrical / Optical Characteristic Curves **(25 °C Ambient Temperature Unless Otherwise Noted)**



Typical Electrical / Optical Characteristic Curves **(25 °C Ambient Temperature Unless Otherwise Noted)**




Fig.10 FORWARD CURRENT VS. FORWARD VOLTAGE




Fig.11 FORWARD CURRENT VS. FORWARD VOLTAGE




Fig.12 FORWARD CURRENT DERATING CURVE




Fig.13 RELATIVE LUMINOUS INTENSITY VS. FORWARD CURRENT




Fig.14 RELATIVE LUMINOUS INTENSITY VS. FORWARD CURRENT




Fig.15 SPATIAL DISTRIBUTION




Fig.16 LUMINOUS INTENSITY VS. AMBIENT TEMPERATURE




Fig.17 LUMINOUS INTENSITY VS. AMBIENT TEMPERATURE