


PANEL CUTOUT
MAX. PANEL THICKNESS
10.0mm [.43]


SWITCH FUNCTION	
POS. 1	POS. 2
ON	ON
1-3, 4-6	1-2, 4-5




▲ DPDT ON-ON
CONTACT CONFIGURATION

NOTE:



- ALL DIMENSIONS IN mm [INCH]
- GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- TERMINAL NUMBERS FOR REF ONLY
- CONTACT MATERIAL: SILVER
- RATING: 2A 24VDC
- ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES
AT FULL LOAD.
- INSULATION RESISTANCE: 1,000 M Ω MIN.
- DIELECTRIC STRENGTH: 1,500 VAC MIN. FOR 1 MINUTE
- CONTACT RESISTANCE: 50m Ω MAX. @ 1A 12VDC
- OPERATING TEMP.: -20°C to 55°C
- ▲ DENOTES CRITICAL PARAMETER.
- INGRESS PROTECTION: IP65
- HARDWARE SUPPLIED: O-RING AND HEXNUT



▲ SELECTOR
ACTUATOR FINISH:
STAINLESS STEEL



▲ BODY FINISH:
STAINLESS STEEL



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
B	ECO-102081	ACTUATOR DIMS CHANGE TO REFERENCE	07/13/23	JS	TITLE PVK4S22A0SS				100122494
					SCALE	DATE	DR	DWG	REV
					1:1	7/29/2022	MJR	52-PVK4S22A0SS	B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED