










PI FILM FOR PICK UP,
FOR PN 2-215876-4 ONLY.



[VIEW SHOWN IS CIRCUIT (NON-COMPONENT) SIDE OF BOARD]
PRINTED CIRCUIT BOARD THICKNESS: 1.6mm NOMINAL.
TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.05



LOC	DIST	REVISIONS						
1R	-	P	LTR	DESCRIPTION	DATE	DWN	APP	
			AA1	ECR-10-026537	08AUG11	KK	HMF	
			AA2	ECR-13-013525	29AUG2013	CW	SH	
			AA3	REVISE PER ECO-12-008315	11MAY2015	AD	SH	
			AA4	ADD PN 2-215876-4 WITH TAPE REEL PACKAGE	29SEP2020	IT	SH	

TAPE AND REEL 800 PCS/REEL 6 7	6 POS./ 6 CONTACTS	OVERALL: Ni 1.27 μm MIN. ALL OVER THE CONTACTS SOLDER ZONE: Sn 2.5 μm MIN. ON THE SOLDER ZONE OF THE CONTACT MATING ZONE: PLATING CONFIRMS TO PRODUCT REQUIREMENTS AS PER SPECIFICATION 108-19064	HOUSING COLOR BLACK HOUSING AND CONTACT INSERT: UL 94-V0 HOUSING PA 4.6 CONTACT INSERT: PCT CONTACTS: PH-BRONZE	2-215876-1
TAPE MOUNTED 800 PCS/REEL	6 POS./ 6 CONTACTS			2-215876-3
BULK PACKED 1000 PCS IN A BOX 5	SUPERSEDED BY 215876-3			2-215876-1
240 PIECES IN A TRAY	6 POS./ 6 CONTACTS			OBSELETE 2-215876-0
BULK PACKED 1000 PCS IN A BOX 5	SUPERSEDED BY 215876-1		HOUSING COLOR BLACK PBT, UL 94 V-0 CONTACT INSERT: PBT, UL 94 V-0 CONTACTS: Ph-BRONZE	3-215876-1
240 PIECES IN A TRAY	6 POS./ 6 CONTACTS			1-215876-3
108 PCS IN A MULTI-TUBE	SUPERSEDED BY 1-215876-3			1-215876-1
TAPE MOUNTED 800 PCS/REEL	6 POS./ 6 CONTACTS			215876-1
PACKAGING	REMARKS	FINISH	MATERIAL	P/N









THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 24 SEP 96 G.CONSTANT CHK 24 SEP 96 G.CONSTANT		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED: APVD - R.SMEETS PRODUCT SPEC 108-19064 APPLICATION SPEC 114-19019		NAME MODULAR JACK, SIDE ENTRY, 6/6 FOR PRINTED CIRCUIT BOARD	
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		SIZE A2	
MATERIAL -		FINISH -		CAGE CODE -	
		WEIGHT -		DRAWING NO C=215876	
CUSTOMER DRAWING				SCALE 1:1	SHEET 1 OF 4
				REV AA	

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
IR	-		-	SEE SHEET 1	-	-	-
			-	-	-	-	-

- 1 SEE SHEET 4 FOR MODULAR JACK 6 POS./4 CONTACTS WITH CONTACT COVER.
- 2 FOR APPLICATION INFORMATION SEE SPEC. 114-19019.
- 3 FOR PERFORMANCE REQUIREMENTS SEE SPEC. 108-19064.
- 4 TOLERANCES UNLESS OTHERWISE SPECIFIED: $\pm 0,15\text{mm}$.

5

TRUE POSITIONING WILL NOT BE GUARANTEED USING THIS PACKAGING TYPE.



OBSOLETE

OBSOLETE

OBSOLETE

BULK PACKED 1000 PCS IN A BOX			HOUSING COLOR BLACK PBT, UL94 V-0	5-215876-4
240 PIECES IN A TRAY	6 POS./ 6 CONTACTS	IN CONTACT AREA: 1,2 µm MIN. SEL. GOLD OVER 1,2 µm MIN. NICKEL	CONTACT INSERT: PBT, UL94 V-0	5-215876-3
TAPE MOUNTED 800 PCS/REEL		SOLDER TINES: 2,5 µm MIN. TIN OVER 1,2 µm MIN. NICKEL	CONTACT COVER: PBT, UL94 V-0	5-215876-1
PACKAGING	REMARKS	FINISH	MATERIAL	P/N

PRINTED CIRCUIT BOARD LAYOUT (6 POS./6 CONTACTS)

[VIEW SHOWN IS CIRCUIT (NON-COMPONENT) SIDE OF BOARD]
PRINTED CIRCUIT BOARD THICKNESS: 1,6mm NOMINAL.
TOLERANCES UNLESS OTHERWISE SPECIFIED: $\pm 0,05$

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P. Willems 10-OCT-05	TE Connectivity		
		CHK P. Willems 10-OCT-05			
		APVD J. Broeksteeg 10-OCT-05	NAME MODULAR JACK, SIDE ENTRY, 6/6 FOR PRINTED CIRCUIT BOARD WITH CONTACT COVER		
		PRODUCT SPEC 108-19064			
		APPLICATION SPEC 114-19019	SIZE A2	CAGE CODE	DRAWING NO
		WEIGHT -	C=215876		RESTRICTED TO -
		CUSTOMER DRAWING	SCALE 4:1	SHEET 3 OF 4	REV AA4

