



LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AJ	16	C1		REVISED PER ECO-06-018704	06SEP2006	MC JH



- 1 ZINC PER QQ-Z-363.
- 2 POLYMETHYLPENTENE, GENERAL PURPOSE.
- 3 BERYLLIUM COPPER PER QQ-C-530.
- 4 BRASS PER ASTM-B-453.
- 5 BRASS PER ASTM-B-16.
- 6 NICKEL PLATE PER QQ-N-290, 3.81 μm [.000150] MINIMUM THICK.
- 7 TIN PLATE PER ASTM-B-545, 3.81 μm [.000150] MINIMUM THICK.
- 8 GOLD PLATE PER MIL-G-45204, 0.76 μm [.000030] MINIMUM THICK.
- 9. SEE INSTRUCTION SHEET 2769.



RECOMMENDED PANEL CUTOUT

PCB CONFIGURATION

OBSOLETE	2.03±0.13 [.080±.005]	2.29±0.13 [.090±.005]	414907-3
	2.03±0.13 [.080±.005]	2.79±0.25 [.110±.010]	414907-2
	3.48±0.25 [.137±.010]	4.11±0.43 [.162±.017]	414907-1
B		A	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. LIPPERT 7-7-94 CHK M. TOMCHAK 7-7-94 APVD J. LIPPERT 7-7-94	tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.20 [.008] 3 PLC ± - 4 PLC ± - ANGLES ± -	NAME PRODUCT SPEC APPLICATION SPEC	JACK, RIGHT ANGLE, 75 OHM, LOW PROFILE, PCB, BNC -
MATERIAL SEE NOTES 1 - 5	FINISH SEE NOTES 6 - 8	SIZE CAGE CODE DRAWING NO WEIGHT -	RESTRICTED TO A1 00779 C=414907
CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1 REV C1