





CONNECTOR DESIGNATORS

A-B*-C-D-E-F

G-H-J-K-L-S

* Conn. Desig. B See Note 3

DIRECT COUPLING



440-031
EMI/RFI Banding and Shrink Boot Adapter
Direct Coupling - Split Shell



440

See inside back cover fold-out or pages 13 and 14 for Tables I and II.

TABLE III: FRONT ADAPTER			
Shell Size	J Max - Conn. Designator		
	A-E-F J-H-L-S	D-B-G-K	C
08/09	1.180 (30.0)	1.250 (31.8)	
10/11	1.180 (30.0)	1.250 (31.8)	
12/13	1.180 (30.0)	1.250 (31.8)	1.735 (44.1)
14/15	1.180 (30.0)	1.250 (31.8)	1.915 (48.6)
16/17	1.380 (35.0)	1.560 (39.6)	1.915 (48.6)
18/19	1.380 (35.0)	1.560 (39.6)	1.915 (48.6)
20/21	1.380 (35.0)	1.560 (39.6)	1.915 (48.6)
22/23	1.380 (35.0)	1.560 (39.6)	1.915 (48.6)
24/25	1.380 (35.0)	1.560 (39.6)	1.915 (48.6)
28/29	1.610 (40.9)	1.560 (39.6)	1.915 (48.6)
32/33	1.610 (40.9)	1.750 (44.5)	1.915 (48.6)
36	1.610 (40.9)	1.750 (44.5)	1.915 (48.6)
40	1.610 (40.9)	2.190 (55.6)	1.915 (48.6)

TABLE IV: ELBOW DIMENSIONS					
Dash No.	E Max	F Max	G Max	H Max	
01	.440 (11.2)	1.635 (41.5)	.680 (17.3)	1.575 (40.0)	
02	.440 (11.2)	1.635 (41.5)	.680 (17.3)	1.575 (40.0)	
03	.440 (11.2)	1.635 (41.5)	.680 (17.3)	1.575 (40.0)	
04	.440 (11.2)	1.635 (41.5)	.680 (17.3)	1.575 (40.0)	
05	.500 (12.7)	1.695 (43.1)	.750 (19.1)	1.635 (41.5)	
06	.500 (12.7)	1.695 (43.1)	.750 (19.1)	1.635 (41.5)	
07	.560 (14.2)	1.765 (44.8)	.810 (20.6)	1.705 (43.3)	
08	.560 (14.2)	1.765 (44.8)	.810 (20.6)	1.705 (43.3)	
09	.620 (15.7)	1.795 (45.6)	.870 (22.1)	1.735 (44.1)	
10	.680 (17.3)	1.895 (48.1)	.930 (23.6)	1.835 (46.6)	
11	.680 (17.3)	1.895 (48.1)	.930 (23.6)	1.835 (46.6)	
12	.750 (19.1)	1.955 (49.7)	1.000 (25.4)	1.895 (48.1)	
13	.820 (20.8)	2.015 (51.2)	1.060 (26.9)	1.955 (49.7)	
14	.820 (20.8)	2.015 (51.2)	1.060 (26.9)	1.955 (49.7)	
15	.880 (22.4)	2.075 (52.7)	1.120 (28.4)	2.015 (51.2)	
16	.880 (22.4)	2.075 (52.7)	1.120 (28.4)	2.015 (51.2)	

TABLE V: CABLE ENTRY						
Dash No.	K		L		M	
01	.125	(3.2)	.250	(6.4)	.312	(7.9)
31	.188	(4.8)	.312	(7.9)	.374	(9.5)
02	.250	(6.4)	.375	(9.5)	.437	(11.1)
32	.312	(7.9)	.438	(11.1)	.500	(12.7)
03	.375	(9.5)	.500	(12.7)	.562	(14.3)
33	.438	(11.1)	.562	(14.3)	.624	(15.8)
04	.500	(12.7)	.625	(15.9)	.687	(17.4)
34	.562	(14.3)	.688	(17.5)	.750	(19.1)
05	.625	(15.9)	.750	(19.1)	.812	(20.6)
35	.688	(17.5)	.812	(20.6)	.874	(22.2)
06	.750	(19.1)	.875	(22.2)	.937	(23.8)
36	.812	(20.6)	.938	(23.8)	1.000	(25.4)
07	.875	(22.2)	1.000	(25.4)	1.062	(27.0)
37	.938	(23.8)	1.062	(27.0)	1.124	(28.5)
08	1.000	(25.4)	1.125	(28.6)	1.187	(30.1)
38	1.062	(27.0)	1.188	(30.2)	1.250	(31.8)
09	1.125	(28.6)	1.250	(31.8)	1.312	(33.3)
10	1.250	(31.8)	1.375	(34.9)	1.437	(36.5)
11	1.375	(34.9)	1.500	(38.1)	1.562	(39.7)
12	1.500	(38.1)	1.625	(41.3)	1.687	(42.8)
13	1.625	(41.3)	1.750	(44.5)	1.812	(46.0)
14	1.750	(44.5)	1.875	(47.6)	1.937	(49.2)
15	1.875	(47.6)	2.000	(50.8)	2.062	(52.4)
16	2.000	(50.8)	2.125	(54.0)	2.187	(55.5)

*Equivalent boot may be supplied in lieu of stated part number.

1. Metric dimensions (mm) are indicated in parentheses.
2. See page 40 for Shrink Boot Reference Information.
3. When using Connector Designator B refer to pages 18 and 19 for part number development.
4. Backshells supplied with 600-052-* band, see Glenair Series 600 Tool Catalog for installation.