





LOC		DIST		REVISIONS			
P	T	L	TR	DESCRIPTION	DATE	DWN	APVD
	B			REV PER ECO 15-005907	5-18-15	CT	DM

RAISED NUMBERS FOR IDENTIFICATION OF CIRCUIT HOLES.



1. MAXIMUM WIRE INSULATION TO BE USED WITH THIS PLUG IS .068 DIA.
2. STAINLESS STEEL RETENTION CLIPS ARE INCLUDED IN INSERTS.
3. THIS PLUG WILL ACCEPT SIZE 20 PIN CONTACT M39029/64-369 OR AMP PART NUMBER 205089-1.
4. UL/CSA DESIGNATION MARKED IN THIS AREA, OPTIONAL
5. FINISH: CADMIUM PER QQ-P-416
6. FINISH: ZINC PLATED PER ASTM-B-633, .000200-.000400 THK WITH SUPPLEMENTARY CHROMATE (Cr3+)



DETAIL T
SCALE 6:1

PLATED PER 6	5-1484949-1
PLATED PER 5	1484949-1
DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 8-28-02	TE Connectivity	
DIMENSIONS: INCHES		CHK D.MILLER 8-28-02		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D.MILLER 8-28-02	NAME	
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± ± 8° 30°	PRODUCT SPEC	RCPT. ASSEMBLY,AMPLIMITE 25 POSN,SIZE 3, SERIES 109 BLINDMATE, REVERSE GENDER	
MATERIAL SEE CALLOUTS		APPLICATION SPEC	SIZE	RESTRICTED TO
		WEIGHT	CAGE CODE	DRAWING NO
			A1	00779
			1484951	
			CUSTOMER DRAWING	SCALE 4:1 SHEET 1 OF 1 REV B