





① MATERIALS AND FINISH:
HOUSING: HIGH TEMPERATURE POLYAMIDE, UL 94V-0 RATED,
COLOR: BLACK.
TERMINAL: COPPER ALLOY, TIN PLATED.
CLAMP: COPPER ALLOY, NICKEL PLATED.
CLAMPING SCREW: COPPER ALLOY, NICKEL PLATED.

2. WIRE SIZE RANGE: 16-28 AWG.

3. CURRENT RATING: 12A, 150V
OPERATING TEMPERATURE: -40°C TO +110°C

4. SUITABLE FOR 2.4mm MAX PC BOARD THICKNESS.



3.5	45.72	12	3-1776113-2
	41.91	11	3-1776113-1
	38.10	10	3-1776113-0
	34.29	9	2-1776113-9
	30.48	8	2-1776113-8
	26.67	7	2-1776113-7
	22.86	6	2-1776113-6
	19.05	5	2-1776113-5
	15.24	4	2-1776113-4
	11.43	3	2-1776113-3
2.6	7.62	2	2-1776113-2
	45.72	12	1-1776113-2
	41.91	11	1-1776113-1
	38.10	10	1-1776113-0
	34.29	9	1776113-9
	30.48	8	1776113-8
	26.67	7	1776113-7
	22.86	6	1776113-6
	19.05	5	1776113-5
	15.24	4	1776113-4
DIM A	11.43	3	1776113-3
	7.62	2	1776113-2
	L	NO OF POSN	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 02JUN2005 S. WELDON		TE Connectivity	
DIMENSIONS:		CHK 02JUN2005 C. RICHARD		NAME TERMINAL BLOCK, PCB MOUNT, STRAIGHT, 8.5mm PROFILE, SIDE WIRE ENTRY, 3.81mm PITCH	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 02JUN2005 C. RICHARD			
mm		PRODUCT SPEC			
		- APPLICATION SPEC		SIZE	
0 PLC ± 1 PLC ±0.3 2 PLC ±0.25 3 PLC ±0.000 4 PLC ±0.000 ANGLES ± FINISH		- WEIGHT		CAGE CODE	
MATERIAL		- CUSTOMER DRAWING		DRAWING NO	
		- 		A2 00779 C-1776113	
				RESTRICTED TO	
				- SCALE 6.1 SHEET OF REV P	