








PANEL THICKNESS	(X) DIM.
0.75 TO 1.25	20.2mm
1.25 TO 2.00	20.4mm
2.00 TO 3.00	20.6mm



▲ SWITCH FUNCTION		
POS. 3	POS. 2	POS. 1
ON	OFF	ON
2-1	OPEN	2-3



NOTE:

1. DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ±0.4
X.XX = ±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT MATERIAL: SILVER
- ▲ 5. CONTACT RATING: ANSI/UL 1054 CAN/USA C22.2 NO. 55 [E194579]:
10A @ 250VAC (UR, cUR)
EN 61058-1: 2002:
6(2)A 250~μ 1E4 T125/55 [ENEC14]
6. CONTACT RESISTANCE: 35mΩ MAX. @ 50VAC
7. INSULATION RESISTANCE: 100MΩ MIN. @ 500VAC
8. DIELECTRIC STRENGTH: 1,500VAC FOR 1 MINUTE
9. ELECTRICAL LIFE: 6,000 CYCLES [UR, cUR]
10,000 CYCLES [ENEC14]
10. OPERATING TEMP.: -20°C to 105°C [UR, cUR]
-20°C to 85°C [ENEC14]
11. ▲ DENOTES CRITICAL PARAMETER
12. ILLUMINATION VOLTAGE: N/A



A	23775	RELEASE FOR PRODUCTION	2/14/19	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE RR1153112S

SCALE 2:1	DATE 2/14/2019	DR MW	DWG 38-RR1153112S	REV A
--------------	-------------------	----------	----------------------	----------