






MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []


Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



SILVER PLATED MOUNTING HARDWARE



LOCK WASHER



M5X .8 - 6H
AFTER
PLATING
HEX NUT

5500	350	100	10 A	I.R. MIN. @ 100 (VDC.)	DWV	20	65	70	70
	85°C	125 °C				10 MHz	100 MHz	1 GHz	10 GHz
MIN. CAP. (pF)	WORKING VOLTAGE (WVdc)		CURRENT IDC	10 G Ω	700 vdc	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD -220			

REVISION RECORD	Original Release C.O. 4668	0	TUSONIX TUCSON, ARIZONA -- TOLERANCES -- Unless Otherwise Specified 2 Place Decimal ± 3 Place Decimal ± .031 [0.79] Angles ±							Title BUSHING STYLE EMI FILTER	
	WVDC 85° C WAS 200. E.C. 03-18-97	1									
	RDN TO COMP FMT & ADDED L WASHER, HET NUT & NOTE 1. S.M. 10-20-98	2									
	19981019-5-01 ADDED METRIC, CIRCUIT & ORIENTATION. S.M. 12-18-01	3									
	20011210-2-04 CAP WAS 5000. FIXED METRIC 2 PLCS. S.M. 07-14-03	4									
20030711-1-01 SOLDER PLATED, SOLDER PLATED COPPER, SILVER PLATED BRASS & IR MIN. @ 100 VDC & DWV COLUMNS ADDED & NOTE DELETED L.E. 01-30-04	20040130-1-01	5	TUSONIX TUCSON, ARIZONA -- TOLERANCES -- Unless Otherwise Specified 2 Place Decimal ± 3 Place Decimal ± .031 [0.79] Angles ±							A	4209-053