


NOTES: UNLESS OTHERWISE SPECIFIED

1. FOR USE WITH BELDEN 9529, 1505A & 1805F CABLES.
2. FOR CABLING INSTRUCTIONS SEE 3-661-1.
3. FOR CABLE TRIMMING USE KTJ-57 & KTD-26.
4. FOR CRIMPING USE DIE KTH-2261.
5. INTERFACE PER KINGS ES-17, FIG. 6
6. MATERIAL SPECIFICATIONS:
INSULATOR: TEFLON, ASTM-D-4894 OR ASTM D1710
GASKET: SILICONE RUBBER, A-A-59588
SPRING WASHER, OUTER CONTACT: BERYLLIUM COPPER PER ASTM B196
K-GRIP SLEEVE: COMMERCIAL BRONZE, ASTM B135
ALL OTHER METAL PARTS: BRASS PER ASTM B16
7. FINISH SPECIFICATIONS:
CENTER CONTACT: GOLD PLATE PER MIL-G-45204
SPRING WASHER: SILVER PLATE PER QQ-S-365 OR NICKEL PLATE PER QQ-N-290
ALL OTHER METAL PARTS: NICKEL PLATE PER QQ-N-290
8. ELECTRICAL SPECIFICATIONS:
IMPEDANCE: 75 OHMS
WORKING VOLTAGE: 500 VOLTS RMS
FREQUENCY RANGE: DC - 12 GHz
RETURN LOSS: -30dB MAX TO 3.0 GHz
-20dB MAX TO 6.0 GHz
9. COMPLIANT TO 3G/6G/12G SDI SMPTE REQUIREMENTS.

REV	DESCRIPTION	BY DATE	APPD
P	ER057798	04/10/15	VA



MARK: KINGS 2065-2-9 (DATE CODE)

CATALOG P/N: 2065-2-9

PER ASME Y14.5M-1994 UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES [MM] TOLERANCES: DECIMAL: .XX [X.X] ± .01 [0.25] .XXX [X.XX] ± .004 [0.10] .XXXX [X.XXX] ± .XXXX ANGLES: ± 2° SCALE: 4:1				KINGS by WINCHESTER Winchester Electronics Corporation ELECTRONICS 199 Park Road Ext Suite 104 Middlebury, Connecticut 06762			
CUSTOMER SALES DRAWING				75 OHM BNC PLUG FOR BELDEN 1505A OR EQUIVALENT CABLE (RoHS)			
DRAWN	DATE	APPROVED	DATE	A SD2065-2-9 SHT OF REV 1 1 P			
TML	01/11/99	DCI	01/11/99				
APPROVED	DATE	APPROVED	DATE				
XXX	XX/XX/XX	XXX	XX/XX/XX				