




REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
K	PRODUCT DRAWING (EAR 13638)	DEC09/09	K.L.
L	PRODUCT DRAWING (EAR 14330)	DEC11/14	K.L.



ORDERING CODE: M R J - 5 3 X X - X 1

SERIES, RUGGED RJ
 RECEPTACLE, RIGHT ANGLE, PCB TAIL
 NUMBER OF CONTACTS
 8= 8 CONTACTS
 A=10 CONTACTS
 LED OPTION
 0=NONE
 1=GREEN LEFT, YELLOW RIGHT
 4=YELLOW LEFT, GREEN RIGHT
 5=GREEN LEFT, GREEN RIGHT
 A=BI-COLOUR GREEN/YELLOW LEFT
 BI-COLOUR GREEN/YELLOW RIGHT
 D=GREEN LEFT
 BI-COLOUR GREEN/YELLOW RIGHT
 E=YELLOW LEFT
 BI-COLOUR GREEN/YELLOW RIGHT

TAIL LENGTH AND MOUNTING
 HOLE THREAD OPTION
 0= TAIL LENGTH A=2.54 [.100],
 #4-40 UNC THREAD
 B= TAIL LENGTH A=3.81 [.150],
 #4-40 UNC THREAD
 M= TAIL LENGTH A=2.54 [.100],
 M3 x 0.5 THREAD
 P= TAIL LENGTH A=3.81 [.150],
 M3 x 0.5 THREAD

SINGLE PORT

NOTES:

- MATERIAL:
 ALL MATERIALS ARE RoHS COMPLIANT PER EU DIRECTIVE 2011/65/EU AND AMENDMENTS
 - SHELL - DIECAST ZINC, NICKEL PLATED
 - CONTACTS - PHOSPHOR BRONZE WITH 50 MICROINCHES (1.27 MICRONS) GOLD OVER 50 MICROINCHES (1.27 MICRONS) MINIMUM NICKEL ON THE MATING AREA AND MATTE TIN OVER NICKEL ON THE CONTACT TAILS.
 - INSERTS - ENGINEERING THERMOPLASTIC, UL FLAMMABILITY RATING 94V-0, REAR INSERTS: BLACK NYLON, FRONT INSERT: CLEAR POLYCARBONATE
 - LED'S - EPOXY LENS, STEEL TAILS WITH TIN PLATING
 - GASKET - SILICONE RUBBER, BLACK
- ENVIRONMENTAL PERFORMANCE PER IEC 60529 CODE IP67 FOR SEAL BETWEEN MATING AREA AND PCB SIDE OF CONNECTOR. GASKET PROVIDES SEAL TO INSIDE FACE OF PANEL.
- CURRENT RATING: 1.5 AMPERES
- CONTACT RESISTANCE: 30 MILLIOHMS MAXIMUM
- OPERATING TEMPERATURE: -40°C TO +105°C
- LED CHARACTERISTICS: FORWARD DC CURRENT 25 mA MAX., FORWARD VOLTAGE 2.5 V MAX@ 2 mA
- AVAILABLE MATING AREA COVERS PROVIDE ADDED PROTECTION. CONSULT WITH AMPHENOL CANADA FOR DETAILS.
- CUSTOMER TO VERIFY THAT ALL PROCESS CLEANERS ARE COMPATIBLE WITH POLYCARBONATE MATERIAL.

SPECIAL CONNECTORS
 MANY UNIQUE FEATURES ARE READILY AVAILABLE TO SUIT CUSTOMER REQUIREMENTS. CONSULT WITH AMPHENOL CANADA FOR DETAILS.

UNLESS SPECIFIED OTHERWISE	DRAWN	S.SEMENOV	NOV11/04
PRIMARY UNITS MILLIMETERS	CHECKED		
SECONDARY INCHES	M.E. APP'D		
REFERENCE IN PARENTHESES	Q.A. APP'D		
GENERAL TOLERANCES	DWG APPR.	A. GREEN	NOV11/04
1 DECIMAL PLACE	ENG. REL. NO.		
2 DECIMAL PLACES ±0.15	REF.		
3 DECIMAL PLACES	THIRD ANGLE PROJECTION		
ANGULAR DEGREES	DO NOT SCALE DRAWING		

Amphenol Canada Corp. www.amphenolcanada.com			
MRJ SERIES RUGGED MODULAR JACK, 8 & 10 POSITION RIGHT ANGLE, WITH LED, TAIL LENGTH & THREAD OPTIONS, RoHS COMPLIANT			
P-MRJ-53XX-X1			REV L
CODE ID NO. 03554	DWG SIZE: C	SCALE: 3:1	SHEET 1 OF 2





RECOMMENDED P.C.B. LAYOUT COMPONENT SIDE OF BOARD





REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
K	PRODUCT DRAWING (EAR 13638)	DEC09/09	K.L
L	PRODUCT DRAWING (EAR 14330)	DEC11/14	K.L

8 POSITION VIEW





8 POSITION LED SCHEMATIC GREEN OR YELLOW

10 POSITION VIEW



10 POSITION LED SCHEMATIC GREEN OR YELLOW



UNLESS SPECIFIED OTHERWISE		DRAWN	S. SEMENOV	NOV11/04
PRIMARY	UNITS MILLIMETERS	CHECKED		
SECONDARY	INCHES	M.E. APP'D		
REFERENCE	IN PARENTHESES	Q.A. APP'D		
GENERAL TOLERANCES		DWG APPR.	A. GREEN	NOV11/04
1	DECIMAL PLACE	ENG. REL. NO.		
2	DECIMAL PLACES ± 0.15	REF.		
3	DECIMAL PLACES	THIRD ANGLE PROJECTION		
ANGULAR DEGREES		DO NOT SCALE DRAWING		

Amphenol Canada Corp. www.amphenolcanada.com	
MRJ SERIES RUGGED MODULAR JACK, 8 & 10 POSITION RIGHT ANGLE, WITH LED, TAIL LENGTH & THREAD OPTIONS, RoHS COMPLIANT	
DWG. NO.	REV L
P-MRJ-53XX-X1	
CODE ID NO. 03554	DWG SIZE: C
SCALE: 3:1	SHEET 2 OF 2