


** Not all features are shown in this drawing. For more detailed information, please contact your Fair-Rite representative.

UNCONTROLLED ~CATALOG~ DRAWING

SIZE	PART NO.	REV.
B	2752555577	~



DIMENSIONS
BOLD NUMBERS ARE IN MILLIMETERS
LIGHT NUMBERS ARE IN INCHES

ELECTRICAL SPECIFICATIONS

IMPEDANCE [Ohms]		
100 MHz	250 MHz	500 MHz
530 Min.	640 Min.	375 Min.

NOTES:

- 1 - PARTS MEET FAIR-RITE PRODUCTS VISUAL INSPECTION CRITERIA FOR GENERIC SURFACE MOUNT BEADS
- 2 - PARTS MEET FAIR-RITE PRODUCTS CORP. SOP# ELC-27, FOR THERMAL SHOCK RESISTANCE.
- 3 - WIRE MUST MEET SOLDERABILITY SPECIFICATIONS WHEN TESTED PER FAIR-RITE PRODUCTS CORP. SOP# ELC-57.
- 4 - PACKAGING: THIS PART IS SUPPLIED TAPED AND REELED
- 5 - IMPEDANCE IS MEASURED ON A HP4191A USING A 16092A TEST FIXTURE, WITH FIXTURE COMPENSATION.

FAIR-RITE PRODUCTS CORP.				
TITLE 2-1/2 TURN SM WIDE BAND CHOKE				
DRAWN BY D. FOOTE	DATE 8/28/2019	SIZE B	PART NO. 2752555577	REV. ~
CHKD BY				
APPRVD BY		SCALE: NONE	SHEET 1 OF 1	

FR# 52