


CMS04N06Y-HF

N-Channel

RoHS Device

Halogen Free





Features

- Advanced trench process technology.
- High density cell design for ultra low on-resistance.

Mechanical data

- Case: SOT-223 Package.
- Terminals: Solderable per MIL-STD-750, method 2026.
- Weight: 0.123 grams (approx.).

Circuit diagram



Maximum Ratings

Parameter		Symbol	Value	Unit
Drain-source voltage		V_{DS}	60	V
Gate-source voltage		V_{GS}	± 20	V
Continuous drain current	$T_A = 25^\circ\text{C}$	I_D	4	A
	$T_A = 70^\circ\text{C}$		3.2	
Pulsed drain current (Note1)	$T_A = 25^\circ\text{C}$	I_{DM}	8	A
Power dissipation	$T_A = 25^\circ\text{C}$	P_D	3.1	W
	$T_A = 70^\circ\text{C}$		2	W
Typical thermal resistance	Junction to ambient (Note 5)	$R_{\theta JA}$	40.3	$^\circ\text{C/W}$
Operating junction temperature range		T_J	-55 to +150	$^\circ\text{C}$
Storage temperature range		T_{STG}	-55 to +150	$^\circ\text{C}$

Value only by maximum junction temperature.

Company reserves the right to improve product design , functions and reliability without notice.

Electrical Characteristics (at $T_J=25^{\circ}\text{C}$ unless otherwise noted)

Parameter	Symbol	Conditions	Min	Typ	Max	Unit
Static						
Drain-source breakdown voltage	BV _{DSS}	V _{GS} = 0V, I _D = 250μA	60			V
Gate threshold voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = 250μA	1.0	1.86	2.5	
Drain-source on-state resistance	R _{DS(on)}	V _{GS} = 10V, I _D = 3.0A		85	100	mΩ
		V _{GS} = 4.5V, I _D = 2.0A		95	110	
Drain-source leakage current	I _{DSS}	V _{DS} = 48V, V _{GS} = 0V			1.0	μA
Gate-source leakage current	I _{GSS}	V _{GS} = ±20V			±100	nA
Dynamic (Note 6)						
Total gate charge	Q _g	V _{DS} = 48V, I _D = 3A , V _{GS} = 4.5V (Note 2,3)		5.1		nC
Gate-source charge	Q _{gs}			1.2		
Gate-drain ("miller") charge	Q _{gd}			1.9		
Input capacitance	C _{iss}	V _{DS} = 15V, V _{GS} = 0V, f = 1.0MHz		509		pF
Output capacitance	C _{oss}			39		
Reverse transfer capacitance	C _{rss}			26		
Turn-on delay time	td _(on)	V _{DS} = 30V, I _D = 3A, V _{GS} = 10V, R _G = 3.3Ω (Note 2,3)		1.6		ns
Turn-on rise time	tr			7.3		
Turn-off delay time	td _(off)			25		
Turn-off fall time	tf			14		
Drain-source diode						
Maximum continuous drain-source Diode forward current	Is				4	A
Diode forward voltage	VSD	Is = 1A, VGS= 0V, TJ = 25°C		0.8	1.2	V

Notes:

- Pulse test: Pulse width $\leq 300\mu s$, Duty cycle $\leq 2\%$.
- Essentially independent of operating temperature typical characteristics.
- Repetitive rating, pulse width limited by junction temperature $T_{J(MAX)}=150^{\circ}\text{C}$.
Ratings are based on low frequency and duty cycles to keep initial $T_J=25^{\circ}\text{C}$.
- The maximum current rating is package limited.
- $R_{\theta JA}$ is the sum of the junction to case and case to ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins. Mounted on a 1 inch² with 2 oz. square pad of copper.
- Guaranteed by design, not subject to production testing.

Rating and Characteristic Curves (CMS04N06Y-HF)

Fig.1 - Output Characteristic




Fig.2 - Transfer Characteristics




Fig.3 - On-Resistance VS. Drain Current




Fig.4 - Source-Drain Diode Forward Voltage




Fig.5 - Gate Charge Characteristics






Fig.6 - Capacitance VS. Drain-Source Voltage



Reel Taping Specification




SOT-223	SYMBOL	A	B	C	d	D	D1	D2
	(mm)	7.05 ± 0.10	7.40 ± 0.10	1.90 ± 0.10	1.55 ± 0.05	330.00 ± 1.00	100.00 ± 0.50	13.00 ± 0.50
	(inch)	0.278 ± 0.004	0.291 ± 0.004	0.075 ± 0.004	0.061 ± 0.002	12.992 ± 0.039	3.937 ± 0.020	0.512 ± 0.020

SOT-223	SYMBOL	E	F	P	P0	P1	T	W	W1
	(mm)	1.75 ± 0.10	5.50 ± 0.05	8.00 ± 0.10	4.00 ± 0.10	2.00 ± 0.10	0.25 ± 0.05	12.00 + 0.15 - 0.10	12.40 + 2.00 - 0.00
	(inch)	0.069 ± 0.004	0.217 ± 0.002	0.315 ± 0.004	0.157 ± 0.004	0.079 ± 0.004	0.010 ± 0.002	0.472 + 0.006 - 0.004	0.488 + 0.079 - 0.000

Company reserves the right to improve product design , functions and reliability without notice. REV:B

Marking Code


Part Number	Marking Code
CMS04N06Y-HF	4N06A



Suggested PAD Layout

SIZE	SOT-223	
	(mm)	(inch)
A	0.81	0.032
B	1.12	0.044
C	2.30	0.091
D	5.98	0.235
E	3.10	0.122

Note: 1. The pad layout is for reference purposes only.



Standard Packaging

Case Type	REEL PACK	
	REEL (pcs)	Reel Size (inch)
SOT-223	2,500	13