


MALE STRAIGHT RECEPTACLE FOR PCB
SOLDER LEGS - FULL DETENT



R222.426.020

Series : SMP




PANEL CUT OUT

A DIA	B DIA	4 holes	mm	
			Maxi	mini
A			0.86	0.79
B			0.98	0.94
C			2.59	2.49



All dimensions are in mm.



COMPONENTS	MATERIALS	PLATINGS (μm)
BODY	STAINLESS STEEL	GOLD 0.5 OVER NICKEL 2
CENTER CONTACT	BERYLLIUM COPPER	GOLD 1.27 OVER NICKEL 1.27
OUTER CONTACT	-	-
INSULATOR	PTFE	-
GASKET	-	-
OTHERS PARTS	-	-
-	-	-
-	-	-

Issue : 0949 B

In the effort to improve our products, we reserve the right to make changes judged to be necessary.



MALE STRAIGHT RECEPTACLE FOR PCB**R222.426.020****SOLDER LEGS - FULL DETENT**

Series : SMP

PACKAGING

Standard	Unit	Other
100	'W' option	Contact us

SPECIFICATION**ELECTRICAL CHARACTERISTICS**

Impedance	50	Ω
Frequency	0-12	GHz
VSWR	1.15* + 0,0000	x F(GHz) Maxi
Insertion loss	0.12*	$\sqrt{F}(\text{GHz})$ dB Maxi
RF leakage	- (	- F(GHz)) dB Maxi
Voltage rating	335	Veff Maxi
Dielectric withstanding voltage	500	Veff mini
Insulation resistance	5000	M Ω mini

ENVIRONMENTAL

Operating temperature	-65/+165	$^{\circ}\text{C}$
Hermetic seal	NA	Atm.cm3/s
Panel leakage	NA	

OTHERS CHARACTERISTICS

Assembly instruction

Others :

*Coaxial Transmission Line Only

MECHANICAL CHARACTERISTICS

Center contact retention	
Axial force – Mating end	6.8 N mini
Axial force – Opposite end	NA N mini
Torque	NA N.cm mini

Recommended torque

Mating	NA N.cm
Panel nut	NA N.cm

Mating life	100 Cycles mini
Weight	0,7200 g

Issue : 0949 B

In the effort to improve our products, we reserve the right to make changes judged to be necessary.



MALE STRAIGHT RECEPTACLE FOR PCB**SOLDER LEGS - FULL DETENT****R222.426.020**

Series : SMP


SOLDER PROCEDURE IN INDUSTRIAL ENVIRONMENT

Suite aux nouvelles directives européennes RoHS, le plomb ne doit plus être utilisé, entre autre, dans les procédés de brasage

Following the new European directives RoHS, lead should not be used any more, in the solder process.

Voici donc la nouvelle pâte à braser et le nouveau profil de température à utiliser :

Here follow the new solder paste and a new temperature profile to be used:

Sn AG4 Cu0.5

Parmeter	Value	Unit
Temperature rising Area	1 - 4	°C/sec
Max Peak Temperature	260	°C
Max dwell time @260°C	10	sec
Min dwell time @235°C	20	sec
Max dwell time @235°C	60	sec
Temperature drop in cooling Area	-1 to - 4	°C/sec
Max dwell time above 100°C	420	sec

Issue : 0949 B

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

