

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	J	RESIN SUPPLIER CHANGED FOR THE HOUSING	20MAY2022	SCB	PS

D

B

C



C

B

B

A

A



RECOMMENDED HOLE LAYOUT

1	.284	.200	2	3	9-102898-0	
2	.684	.600	6	7	8-102898-9	OBSOLETE 6
3	.484	.400	4	5	8-102898-8	
4	.584	.500	5	6	8-102898-7	OBSOLETE 6
5	.384	.300	3	4	8-102898-6	
6	.084	—	—	1	8-102898-5	
7	.184	.100	1	2	8-102898-4	
8	3.984	3.900	39	40	8-102898-3	
9	3.584	3.500	35	36	7-102898-9	
10	3.184	3.100	31	32	7-102898-5	
11	2.984	2.900	29	30	7-102898-3	
12	2.884	2.800	28	29	7-102898-2	
13	2.784	2.700	27	28	7-102898-1	
14	2.684	2.600	26	27	7-102898-0	
15	2.584	2.500	25	26	6-102898-9	
16	2.484	2.400	24	25	6-102898-8	
17	2.384	2.300	23	24	6-102898-7	
18	2.284	2.200	22	23	6-102898-6	
19	2.184	2.100	21	22	6-102898-5	
20	2.084	2.000	20	21	6-102898-4	
21	1.984	1.900	19	20	6-102898-3	
22	1.884	1.800	18	19	6-102898-2	
23	1.784	1.700	17	18	6-102898-1	
24	1.684	1.600	16	17	6-102898-0	
25	1.584	1.500	15	16	5-102898-9	
26	1.484	1.400	14	15	5-102898-8	
27	1.384	1.300	13	14	5-102898-7	
28	1.284	1.200	12	13	5-102898-6	
29	1.184	1.100	11	12	5-102898-5	
30	1.084	1.000	10	11	5-102898-4	
31	.984	.900	9	10	5-102898-3	
32	.884	.800	8	9	5-102898-2	
33	.784	.700	7	8	5-102898-1	

PLATING	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER
---------	---	---	---	------------	----------------------

4	.284	.200	2	3	4-102898-0
5	.684	.600	6	7	3-102898-9
6	.484	.400	4	5	3-102898-8
7	.584	.500	5	6	3-102898-7
8	.384	.300	3	4	3-102898-6
9	.084	—	—	1	3-102898-5
10	.184	.100	1	2	3-102898-4
11	3.984	3.900	39	40	3-102898-3
12	3.884	3.800	38	39	3-102898-2
13	3.784	3.700	37	38	3-102898-1
14	3.684	3.600	36	37	3-102898-0
15	3.584	3.500	35	36	2-102898-9
16	3.484	3.400	34	35	2-102898-8
17	3.384	3.300	33	34	2-102898-7
18	3.284	3.200	32	33	2-102898-6
19	3.184	3.100	31	32	2-102898-5
20	3.084	3.000	30	31	2-102898-4
21	2.984	2.900	29	30	2-102898-3
22	2.884	2.800	28	29	2-102898-2
23	2.784	2.700	27	28	2-102898-1
24	2.684	2.600	26	27	2-102898-0
25	2.584	2.500	25	26	1-102898-9
26	2.484	2.400	24	25	1-102898-8
27	2.384	2.300	23	24	1-102898-7
28	2.284	2.200	22	23	1-102898-6
29	2.184	2.100	21	22	1-102898-5
30	2.084	2.000	20	21	1-102898-4
31	1.984	1.900	19	20	1-102898-3
32	1.884	1.800	18	19	1-102898-2
33	1.784	1.700	17	18	1-102898-1
34	1.684	1.600	16	17	1-102898-0
35	1.584	1.500	15	16	102898-9
36	1.484	1.400	14	15	102898-8
37	1.384	1.300	13	14	102898-7
38	1.284	1.200	12	13	102898-6
39	1.184	1.100	11	12	102898-5
40	1.084	1.000	10	11	102898-4
41	.984	.900	9	10	102898-3
42	.884	.800	8	9	102898-2
43	.784	.700	7	8	102898-1

PLATING	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER
---------	---	---	---	------------	----------------------

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .005
4 PLC ± -
ANGLES ± -

MATERIAL -

SEE TABLE

DWN H. MOLL 16 JULY 87
CHK L.A. MAYER 16 JULY 87
APVD T.C. CLARK 16 JULY 87

NAME

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

HEADER ASSY, MOD II,
UNSHROUDED, COMPLIANT PIN, SINGLE,
ROW .100 C/L, WITH .025 SQ POSTS

SIZE CAGE CODE DRAWING NO
A1 00779 102898

RESTRICTED TO

SCALE 4:1

SHEET 1 OF 1

REV J