




All dimensions are in mm; tolerances according to ISO 2768 m-H

Interface

According to
Mechanically compatible with

IEC 61169-32
RPC-2.40

Documents

Assembly instruction

02 A3

Material and plating

Connector parts

Center contact
Outer contact
Dielectric
Solder sleeve

Material

CuBe
Stainless steel
PEEK
Brass

Plating

Gold, min. 1.27 µm, over chemical nickel
Passivated
Gold, 0.1 µm min.

Technical Data Sheet				Rosenberger			
RPC-1.85		Straight jack		08K121-271S3			
Electrical data Impedance50 Ω FrequencyDC to 65 GHz Return loss≥ 20 dB, DC to 65 GHz Insertion loss≤ 0.05 x √f(GHz) dB Insulation resistance≥ 5 GΩ Test voltage (at sea level)500 V rms Working voltage (at sea level)150 V rms RF-leakage≥ 100 dB up to 1 GHz - Limitations are possible due to the used cable type - Mechanical data Mating cycles≥ 500 Center contact captivation≥ 20 N Coupling test torque1.65 Nm Recommended torque0.80 Nm to 1.10 Nm Environmental data Temperature range-40°C to +85°C Thermal shockIEC 61169-1, Subclause 9.4.4 CorrosionIEC 61169-1, Subclause 9.4.6 VibrationIEC 61169-1, Subclause 9.3.3 ShockIEC 61169-1, Subclause 9.3.14 Moisture resistanceIEC 61169-1, Subclause 9.4.3 RoHScompliant Tooling N/A Suitable cables UT 085 / RTK-FS 085 / RTK-Flex 405 Weight 11.4 g/pce							
While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.							
Draft		Date		Approved		Date	
H. Babinger		25.08.04		F. Reiner		10.07.18	
Rev.		Engineering change number		Name		Date	
b01		18-1026		M. Ruf		06.07.18	
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de						Tel. : +49 8684 18-0 Email : info@rosenberger.de	
						Page	
						2 / 2	