




- NOTES: UNLESS OTHERWISE SPECIFIED
1. FOR GENERAL SERIES SPECIFICATIONS, SEE SD361-0000
 2. DESIGNED FOR USE WITH RG-178, RG-196, OR EQUIVALENT CABLE
 3. MATERIAL SPECIFICATIONS:
INSULATOR: PTFE
BODY AND CONTACT: BERYLLIUM COPPER
ALL OTHER METAL PARTS: BRASS
 4. FINISH SPECIFICATIONS:
CENTER CONTACTS - .000003 MIN THICK GOLD OVER .000050 MIN THICK NICKEL
ALL OTHER METAL - THIN GOLD OVER .000050 MIN THICK NICKEL
 5. ELECTRICAL SPECIFICATIONS:
IMPEDANCE: 50 OHMS
FREQUENCY RANGE: DC-3.0GHz
 6. CAP AND FERRULE SHIPPED LOOSE
 7. CRIMP WITH .128" HEX DIE.

REV	DESCRIPTION	BY	DATE	APPD
01	PRELIMINARY DRAWING PER ER054879	MS	09/10/14	MAR



RECOMMENDED TRIM DIMENSION

CATALOG P/N: 2021A504-178

PER ASME Y14.5M-1994 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [MM] TOLERANCES: DECIMAL: .XX [XX] ± .01 [0.3] .XXX [XXX] ± .005 [0.13] .XXXX [XXXX] ± .000X ANGLES: ± 2° SCALE: 6:1				WINCHESTER Winchester Electronics Corporation 159 Park Road Ext Suite 104 Middlebury, Connecticut 06762			
CUSTOMER SALES DRAWING				SMP, R/A PLUG FOR RG-178 OR EQUIVALENT CABLE (ROHS)			
DRAWN	DATE	APPROVED	DATE	A SD2021A504-178			
MS	09/10/14	MAR	09/10/14				
APPROVED	DATE	APPROVED	DATE				
XXX	XX/XX/XX	XXX	XX/XX/XX	SHIT OF REV 1 1 01			