




- NOTES:
- MATERIAL CONTACTS; PHOSPHORBRONZE
 - MATERIAL HOUSING; GLASSFILLED POLYESTER (GRAY)
 - GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT): 1,27µm NICKEL MIN. AND COMPLIANT PIN SECTION: 0,5µm TIN MIN. FOR PLATING OF MATING SURFACES SEE APPLICABLE SPECIFICATION REFERENCE FOR EACH DASH NUMBER.
 - CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 2.
 - CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 1.
 - CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL III, CENTRAL OFFICE APPLICATIONS.
 - CONNECTOR LUBRICATED WITH TELCORDIA GR-1217-CORE APPROVED LUBRICANT.
 - ASSEMBLY PRINTED WITH P/N AND DATECODE
 - THE MARKING CAN APPEAR ON THE FRONT SIDE OR BACK SIDE.
 - HOLE PATTERN FOR FEMALE CONNECTOR TYPE B-22 COLUMNS
 - 110 PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID
 - ROW "f" 11 PLATED THROUGH HOLES FOR UPERSHIELD
 - SHIELD MOUNTED ON CONNECTOR WITH DOUBLE SIDED ADHESIVE TAPE OR ADHESIVE.
 - BASIC P.N. LOWERSHIELD : 5352468.

COMPONENT SIDE AS SHOWN
RECOMMENDED PCB-HOLE LAY-OUT
SCALE 2,5:1

10x 4,0 = 40,0

22

1

2,0

4x 2,0 = 8,0

EDGE OF P.C.BOARD

21 x 2,0 = 42,0

1,5

Ø 0,05
ALL HOLES

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.van Hoek 23AUG2007	TE Connectivity Ltd.	
		CHK B.Mooij 23AUG2007		
		APVD J.Broeksteeg 23AUG2007		
		PRODUCT SPEC		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2	APPLICATION SPEC	
		Ø PLG ±	108-19082	
		1 PLG ±	114-19029	
		2 PLG ±	WEIGHT 0.000000	
		3 PLG ±	CUSTOMER DRAWING	
		4 PLG ±		
MATERIAL -		FINISH -		

FINISH		MATERIAL		PARTNUMBER	
△△△		△		1857997-9	
△△		△		1857997-4	
△△		△		1857997-1	
Z-PACK 2mm HM TYPE B - 22 COLUMNS PRE-SHIELDED RECEPTACLE		SIZE A2	CAGE CODE 00779	DRAWING NO C=1857997	RESTRICTED TO -
SCALE 5:1				SHEET 1 of 1	REV D

P.C.B. HOLE DIM. COMPLIANT PIN
FOR DETAILS SEE
APPLICATION SPECIFICATION