





COMMENT:
ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT,
IT MAY NEITHER BE DUPLICATED NOR MADE AVAILABLE TO A THIRD PARTY.
AND IT ALSO MAY NOT BE IMPROPERLY USED BY THE RECEIVER, OR A THIRD PARTY.



FExx^{*1)}P21Gy^{*2)}

RoHS compliant
by exemption

e.g. FE25P21G1

*1) xx No. of contacts 09, 15 or 25

*2) y for performance classes 1,2 or 3
(contact cycle for G1/G2/G3 = 500/200/50)

xx	A [mm]	B [mm]	C [mm]	*E [mm]	*F [mm]	*G [mm]	*H [mm]	*J [mm]
09	31.4	16.9	25	ø 1	ø 3.1	8.5	7.3	2.54
15	39.7	25.2	33.3					
25	53.44	38.9	47.04					

*PCB hole patterns, øE, øF, G, H, J on supplement AM0024

5	2	Clinch nut	4-40 / Brass	tin plated
4	2	Snap-in bracket	Brass	tin plated
3	xx	Signal contact	P21 / Brass	G1/G2/G3
2	1	Shell	Steel	tin plated
1	1	Insulator	PBT (-55°C - +130°C)	grey
No.	St.	Part	Type Description/Material	Surface plating/Colour/Class

				Measurement without tolerance occ. to ISO 2768-m	SCALE 2:1	TITLE Low profile D-Sub Connector	
				NAME / DATE			
			DRAWN	ADenzinger 17-10-2006			
			CHECKED	tschneider01 16-10-2017			
					DWG.NO.	FExxP21Gy	REV.
2	16-10-2017	24017					2
1							
REV.	DATE	CH.-NO.	ORIGINAL: DIN A3-DRAWING AS A FILE		REPLACEMENT FOR:		PAGES 1