



LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPRO
G	14					RELEASED PER 0720-0008-93	2-1-93	18 DAP

METRIC
DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE	UL E13288 Listed
16-14HD AWG STRANDED	16-14HD AWG STRANDED
LR7189 Certified	MILITARY P/N AND CLASS
NOT CERTIFIED	NOT APPLICABLE

△ STAMP AMP 16-14HD* APPROX AS SHOWN



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS
1-800-522-6752
FOR APPLICATION
TOOLING INFORMATION
1-800-722-1111
FOR ORDER ENTRY
1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
170°C MAX
VOLTAGE RATING:
NOT APPLICABLE
WIRE CROSS SECTIONAL AREA RANGE:
1.04-2.62mm² [2.050-5.180] CIR MILS
STRANDED

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON:
2 PLC DEC #
3 PLC DEC #
ANGLES
MATERIAL
COPPER PER
ASTM B-152
ANNEALED
FINISH
TIN PLATE
0.00254 [1.000100] MIN
THK PER MIL-T-10727

DR 2-1-93
1A BRINKMAN
CHK 2-1-93
DA PATTERSON
APPD 2-1-93
DE MILLER
APPD 2-1-93
JL MECKLEY
PRODUCT SPEC
APPLICATION SPEC
WEIGHT
SCALE 4:1

AMP
AMP Incorporated
Harrisburg, PA 17105-3608

TERMINAL, RING TONGUE,
HEAVY DUTY, BUDGET

SIZE
CAGE CODE
00779
DRAWING NO
C-36201
SHEET
1 OF 1