






1. PARTS COMPLY TO AMP SOLDERABILITY SPECIFICATION 109-11-3.
 2. CIRCUIT IDENTIFICATION CHARACTERS ARE ADJACENT TO THE INDICATED CAVITIES, BUT LOCATION AND ORIENTATION MAY DIFFER FROM PRINT.
 3. DIMENSIONS IN BRACKETS ARE IN INCHES.
 4. DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY CONDITION. ADDITIONAL 2% GROWTH DUE TO END USE LOCATION MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.



SECTION A-A



3 DIMENSIONAL MODEL
SCALE 4:1



SECTION B-B

RECOMMENDED MOUNTING HOLE PATTERN
FOR 1.57 [.062] THICK P.C. BOARD
HOLE THAT CORRESPONDS TO REMOVED
CONTACT CAN BE OMITTED

7 3 SOCKET NO OMITTED PHOSPOR BRONZE, PRE-TIN NYLON, UL94V-0,WHITE 1586682-7
3 SOCKET CONTACT MATERIAL AND FINISH NYLON, UL94V-0,WHITE 1586682-3
HOUSING MATERIAL AND COLOR PART NUMBER

7 3 SOCKET NO OMITTED PHOSPOR BRONZE, PRE-TIN NYLON, UL94V-0,WHITE 1586682-7
3 SOCKET CONTACT MATERIAL AND FINISH NYLON, UL94V-0,WHITE 1586682-3
HOUSING MATERIAL AND COLOR PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS THE RESPONSIBILITY OF THE USER TO ENSURE THAT IT IS THE LATEST REVISION
AND THAT IT IS USED IN ITS CURRENT EDITION.
K. WHITAKER 03MAY2005
C. RIDGILL 03MAY2005
S. RIDGILL 03MAY2005
NAME
SOCKET HEADER ASSEMBLY
9 CIRCUIT, SELECTIVELY LOADED,
UNIVERSAL MATE-N-LOK(TM)
DIMENSIONS: mm [INCHES] TOLERANCES UNLESS OTHERWISE SPECIFIED
0 PLC ±.005
1 PLC ±.005
2 PLC ±.005
3 PLC ±.005
4 PLC ±.005
ANGLES ±.005
FINISH
MATERIAL SEE TABLE
SEE TABLE
CAGE CODE DRAWING NO
A/I 00779 C=1586682
CUSTOMER DRAWING
RESTRICTED TO
SCALE 5:1 SHEET 1 OF 1 REV A/I