








REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	ECR-17-011707	14AUG2017	LZ	RR
	A2	ECR-18-006054	26DEC2018	LZ	RR
	B	ECR-19-006634	12JUN2019	LZ	FL
	B1	ECR-21-112328	14SEP2021	SM	FL

NOTES

- MATERIAL: PA66 UL94-V0 GWT750°C NF CTI 350V
- POLARIZATION RIB GO THROUGH TO HINGE.
POSITION "a" OR "b", AT CAVITY NO....
- LOCKING DEVICE FOR COVER AT CAVITY NO
- MATING STOP BETWEEN CAVITY NO 1 AND 2
ALSO BETWEEN THE LAST ONE AND LAST BUT ONE CAVITY
- KEYING RIB POSITION "c" OR POSITION "d"
AT CAVITY NO
- LOCKING LATCH BETWEEN CAVITY NO
- CONTACT CAVITY NO
- AREA FOR TE LOGO
- DIMENSION A AND DIMENSION B SEE TABLE
- CAVITY MARKING
- PRELIMINARY PART NUMBER
- ALTERNATE LOCKING LATCH GEOMETRY
- PRODUCT WITH HIGH RENTENTION FORCE EXCLUDING NOTE 15/LOCKING LATCH STANDARD VERSION:
MORE SPACE FOR LATACH ENGAGEMENT ARE NEEDED IN COUNT PART SIDE.
RECOMMEND SPACE: 4.0mm Min.
- MATERIAL: PA66 UL-94 V0 & GWPEIT 750°C NO FLAME ACCORDING TO IEC 60335-1
- LOCKING LATCH STANDARD VERSION, SEE SHEET 2.
- PART WITH LOW CLOSING FORCE OF TPA: MAX. 75N




POSITION OF KEYING RIB
AND THE LOCKING LATCH
OF THE HOUSING


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Shown Li 12Mar2016	TE Connectivity	
DIMENSIONS:		CHK Federico Lupo 20May2016		
mm		APVD Riccardo Bobone 20May2016	NAME STANDARD-TIMER HOUSING	
		PRODUCT SPEC	-	
		APPLICATION SPEC	-	
MATERIAL		WEIGHT	SIZE A100779	CAGE CODE C=2295787
		CUSTOMER DRAWING	SCALE 3:1	SHEET 1 OF 2
				REV B1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



 SPECIAL LOCKING LATCH GEOMETRY (STANDARD VERSION)
FOR PN 2-2295787-3



Other dimensions please refer to sheet 1



 ONLY FOR 7 POSITION PART





SCALE 2:1

Other dimensions please refer to sheet 1

 5-2295787-7	7	-	35		NATURE
1-2295787-7	7	-	35		
2295787-7	7	07-C	35		
PART NO.	POS.	RAST 5	DIM A	MATERIAL	COLOUR

 5-2295787-5	5	05-B	25		NATURE
2295787-5	5	05-B	25		
 2295787-4	4	-	20		COLOUR
 2-2295787-3	3	-	15		
2295787-3	3	03-G	15		COLOUR
PART NO.	POS.	RAST 5	DIM A		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Shown Li 12Mar2016	 TE Connectivity		
DIMENSIONS:		CHK Federico Lupo 20May2016			
mm		APVD Riccardo Bobone 20May2016	NAME STANDARD-TIMER HOUSING		
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	
		0 PLC ±0.2		APPLICATION SPEC	
		1 PLC ±0.2		SIZE CAGE CODE DRAWING NO	
		2 PLC ±0.2		RESTRICTED TO	
		3 PLC ±		A100779C=2295787	
		4 PLC ±		SCALE 3:1 SHEET 2 OF 2 REV B1	
MATERIAL		WEIGHT		CUSTOMER DRAWING	