






SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
		
ON	ON	(ON)
2-3, 5-6	2-3,5-4	2-1, 5-4

(ON) = MOMENTARY



NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
- TERMINAL NUMBERS FOR REF ONLY
- ▲ PLATING MATERIAL: SILVER
- RATING: 5 AMPS W/RESISTIVE LOAD @ 120VAC OR 28VDC
2 AMPS W/RESISTIVE LOAD @ 250VAC
- ELECTRIC LIFE: 40,000 make-and-break cycles at full load.
- INSULATION RESISTANCE: 1,000 Mega-ohm min.
- DIELECTRIC STRENGTH: 1,000 V RMS @sea level.
- OPERATING TEMP.: -30°C to 85°C
- ▲ DENOTES CRITICAL PARAMETER.
- 2002/95/EC (ROHS) COMPLIANT.



THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

E-SWITCH®

B	16810	FIXED SWITCH FUNCTION	12/29/06	TN
A	16585	RELEASED FOR PRODUCTION	10/30/2006	TN
REV	PCR NO	DESCRIPTION	DATE	BY

TITLE 100DP7T7B13M7QE

SCALE 2:1

DATE 12/29/2006

DR TN

DWG T128085

REV B