






MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



NOTES:

- TUSONIX STANDARD PART NUMBER: 4100-053.
TUSONIX RoHS COMPLIANT PART NUMBER: 4100-053 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
- LEAD FINISH: STANDARD PART #: 60/40 SOLDER PLATED. RoHS PART #: SILVER PLATED.
- PART MARKING: STANDARD PART: NO MARKING.
RoHS PART: GREEN INK DOT ON INSULATION BAND.

Cx 1KHz @ 25°C	WORKING VOLTAGE		I.R. MIN. @ 100 (VDC)	DWV (VAC)	CURRENT Idc (A)	TYPICAL NO LOAD INSERTION LOSS @ 25°C (dB) PER MIL-STD-220			
	+85°C 250 @ 60 HZ VAC	+125°C 200 VDC				1 MHz	10 MHz	100 MHz	1 GHz
10,000/5,000			10 G Ω	350	10 MAX.	2	18	60	70

X-2015 Rev-0	REVISION RECORD																						
	Original Release C.O.		0																				
	WAS SK 6871-001. EC 07-27-88																						
	4056		1																				
	COMPLETELY REVISED & REDRAWN PER SK 6905-000. L.E. 09-29-88																						
	4170		2																				
	DIM. REVISED .200 WAS .175. L.E. 11-10-89																						
	4900		3																				
	RDN TO COMP FMT. S.M. 05-09-00																						
	20000508-2-01		4																				
ADDED NOTES 1-3. S.M. 05-24-05																							
20050513-2-02		5																					
ADDED DWV. S.M. 02-09-06																							
20060109-5-02		6																					
												--TOLERANCES-- Unless Otherwise Specified											
												DECIMAL ± .031 [0.79]											
												ANGLES ± 											
TUSONIX TUCSON, ARIZONA												Title P.C. BOARD MOUNT π TYPE LOW PASS FILTER											
												Drawn S.M. 05-08-00										Scale 4 X	
												Approved T.C. 05-08-00											
A												4100-053											