




TECHNICAL CHARACTERISTICS

1.General Characteristics

Dimensions:12.85LX17.20WX1.38H mm

TRAY MATING FORCE:2~10N

TRAY UNMATING FORCE:4~10N

Durability:1,500 cycles min.

2.Electrical Characteristics

Contact resistance:50mΩ typical,100mΩMax

Insulation resistance:>1000m/500V DC

3.Solderability

Vaporphase:215°C,30sec.Max



IR reflow:260°C,5sec.Max

Manual soldering:370°C.3sec.Max

4.Environmental Characteristics

Operating temperature:-40°C~+85°C

Operating humidity:10%~+95%RH



RECOMMENDED P.C.B. LAYOUT

COMPONENT SIDE(TOLERANCE ±0.05)

PAD AREA

KEEP AREA

NO PATTERN AND VIA HOLE IN THI

NANO SIM CARD	
Pin No.	ASSIGNMENT
C1	VCC(SUPPLY VOLTAGE)
C2	RST(RESET SIGNAL)
C3	CLK(CLOCK SIGNAL)
C5	GND
C6	VPP(VARIABLE SUPPLY VOLTAGE)
C7	I/O(DATA INPUT/OUTPUT)
GND	GND

ITEM	PART NAME	Q'TY	MATERIAL	FINISH
1	HOUSING	1	Hi-temp Thermoplastic	Black UL94V-0
2	DATA CONTACT	6	Copper Alloy	Contact area:Gold plated
3	SHELL	1	Stainless Steel	Solder area:Gold plated

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE:NANO SIM卡托式卡座 1.45H 6PIN 内牌 14.85*12.7*1.45MM	
DECIMALS:		PAR	SMN-337-CRP6
ANGLES:		DWN	Lucas
X.:±0.40		CHKD	Ethan
X.X:±0.20		APVD	Jacob
X.XX:±0.10		SCALE:1:1	UNIT:MM
CUSTOMER COPY		SIZE:A4	SHEET:1F1

Technical drawing of a reinforced concrete slab (Decke) showing dimensions and reinforcement details. The drawing includes a plan view of the slab with four columns and a cross-section view on the right. Dimensions are given in meters. The plan view shows a total width of 24.00m and a total length of 20.00m. The distance between columns is 4.00m. The slab thickness is 0.30m. The reinforcement consists of top bars (Ø 1.50) and bottom bars (Ø 1.50). The cross-section shows a total height of 15.20m and a clear height of 11.50m. The top bars are spaced at 2.00m and 1.75m. The bottom bars are spaced at 2.00m and 1.75m.

4,卷带封合力小于100G.

A diagram of a 'Big Carton' (box) with dimensions 350 (width), 350 (depth), and 400 (height). A large arrow points to the left. A label is attached to the front face, containing the following information:

P/O NO:	
ITEM NO:	PCS
QTY:	PCS
N. P:	PCS
G. P:	CM
MEAS:	

The label is titled 'Label' and the box is titled 'Big Carton'.

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE:NANO SIM卡托式卡座 1.45H	
			6PIN 内焊 14.85*12.7*1.45MM	
DECIMALS:	ANGLES:		PAR	SMN-337-CRP6
X.:±0.40	.X':±3"		DWN	Lucas
X.X:±0.20	.XX':±2"		CHKD	Ethan
X.XX:±0.10		APVD	Jacob	
		CUSTOMER COPY	SCALE1:1	UNIT:MM 
			SIZE:A4	SHEET:1F1
				REV:A