





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	J1	PN 280580-2 REACTIVATED	17MAR2020	KJK	PS

[illegible]

NOTES:

- ① HOUSING: LCP, BLACK, UL94-V0
- ② CONTACTS: PHOSPHOR BRONZE, MIN. 0.38 μ m GOLD ON CONTACT AREA AND GOLD FLASH ALL OVER, OVER NICKEL
- ③ CONTACTS: PHOSPHOR BRONZE, MIN. 0.76 μ m TIN PLATED ALL OVER, EXCEPT FOR CUTTING EDGES.
- ④ THIS MAX. DIMENSION ASSURES PROPER POSITION OF CONNECTOR ON PCB DURING WAVE SOLDERING OPERATION
- ⑤ OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAVI.S 08AUG2019 CHK KARTHIK J K 08AUG2019 APVD PRASHANTH S 08AUG2019		 TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.3mm		NAME AMPMODU II, SINGLE ROW, BOARD TO BOARD RECEPTACLE, HORIZONTAL MOUNT			
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±2°					
MATERIAL - -		FINISH - -		PRODUCT SPEC 108-20025		APPLICATION SPEC -	
		WEIGHT -		SIZE A 3		CAGE CODE 00779	
				DRAWING NO C-281333		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 5:1		SHEET 1 OF 1	
						REV 1	