



		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED (ECO-19-007137)	13MAY19	A.H	W.W
	A2	REVISED (ECO-19-018741)	10DEC19	A.H	W.W
	A3	REVISED (ECO-21-001090)	26JAN21	A.H	I.Y
	A4	REVISED (ECO-21-003425)	17MAR21	A.H	I.Y

CODINGS


CODING A




CODING B









CODING C



CODING J



CODING Z



CODE A AS SHOWN

1 INTERFACE DESIGN ARE ACCORDING TO TE DRAWING: 208-18037

$\triangle_2$ CENTER OF GRAVITY

3 ALL DIMENSIONS IN () FOR INFORMATION ONLY

4 SOLDERING PROCESS: LEAD FREE REFLOW SOLDERING IN REFERENCE TO JEDEC J-STD-020D

△ VACUM GRIP AREA FREE OF SCRATCH

6 PCB TOP LAYER MUST BE GND PLANE, EXCEPT THE NEED SIGNAL PATHES AND CUT OUT AREA

7 MATED WITH TE PLUG X-2333538-X OR X-2334013-X OR X-2317303-X.

8 CUT OUT AREA IS VARIANT FOR CODINGS. DETAIL REFER TO CVM OR
CONTACT WITH TE PRODUCT ENGINEER.

9 TRAY SIZE:350*260*36.7mm.

10 TRAY SIZE:320*125*36.7mm.

/	4-2339800-9 	A	Z	12	PIN	Cu ALLOY	13.96	Ni/Sn	4	
				1	HORIZONTL SHIELD	Cu ALLOY		PRE-TIN	3	
				4	VERTICAL SHIELD	Cu ALLOY		PRE-TIN	2	
	4-2339800-7 	A	J	1	HOUSING	PA4T-GF30	13.96	WATER BLUE	1	
				12	PIN	Cu ALLOY		Ni/Sn	4	
				1	HORIZONTL SHIELD	Cu ALLOY		PRE-TIN	3	
	4-2339800-3 	A	C	4	VERTICAL SHIELD	Cu ALLOY	13.96	PRE-TIN	2	
				1	HOUSING	PA4T-GF30		BLUE	1	
				12	PIN	Cu ALLOY		Ni/Sn	4	
	4-2339800-2 	A	B	1	HORIZONTL SHIELD	Cu ALLOY	13.96	PRE-TIN	3	
				4	VERTICAL SHIELD	Cu ALLOY		PRE-TIN	2	
				1	HOUSING	PA4T-GF30		WHITE	1	
	4-2339800-1 	A	A	12	PIN	Cu ALLOY	13.96	Ni/Sn	4	
				1	HORIZONTL SHIELD	Cu ALLOY		PRE-TIN	3	
				4	VERTICAL SHIELD	Cu ALLOY		PRE-TIN	2	
	3-2339800-9	2-2339800-9 	A	Z	1	HOUSING	PA4T-GF30	13.96	BLACK	1
					12	PIN	Cu ALLOY		Ni/Sn	4
					1	HORIZONTL SHIELD	Cu ALLOY		PRE-TIN	3
	3-2339800-7	2-2339800-7 	A	J	4	VERTICAL SHIELD	STAINLESS STEEL	13.96	Ni/Sn	2
					1	HOUSING	PA4T-GF30		BEIGE	1
					12	PIN	Cu ALLOY		Ni/Sn	4
	3-2339800-3	2-2339800-3 	A	C	1	HORIZONTL SHIELD	Cu ALLOY	13.96	PRE-TIN	3
					4	VERTICAL SHIELD	STAINLESS STEEL		Ni/Sn	2
					1	HOUSING	PA4T-GF30		BLUE	1
3-2339800-2	2-2339800-2 	A	B	12	PIN	Cu ALLOY	13.96	Ni/Sn	4	
				1	HORIZONTL SHIELD	Cu ALLOY		PRE-TIN	3	
				4	VERTICAL SHIELD	STAINLESS STEEL		Ni/Sn	2	
3-2339800-1	2-2339800-1 	A	A	1	HOUSING	PA4T-GF30	13.96	WHITE	1	
				12	PIN	Cu ALLOY		Ni/Sn	4	
				1	HORIZONTL SHIELD	Cu ALLOY		PRE-TIN	3	
1-2339800-9	2339800-9 	A	Z	4	VERTICAL SHIELD	Cu ALLOY	13.96	PRE-TIN	2	
				1	HOUSING	PA4T-GF30		WATER BLUE	1	
				12	PIN	Cu ALLOY		Ni/Sn	4	
1-2339800-7	2339800-7 	A	J	1	HORIZONTL SHIELD	Cu ALLOY	13.96	PRE-TIN	3	
				4	VERTICAL SHIELD	Cu ALLOY		PRE-TIN	2	
				1	HOUSING	PA4T-GF30		BEIGE	1	
1-2339800-3	2339800-3 	A	C	12	PIN	Cu ALLOY	13.96	Ni/Sn	4	
				1	HORIZONTL SHIELD	Cu ALLOY		PRE-TIN	3	
				4	VERTICAL SHIELD	Cu ALLOY		PRE-TIN	2	
1-2339800-2	2339800-2 	A	B	1	HOUSING	PA4T-GF30	13.96	BLUE	1	
				12	PIN	Cu ALLOY		Ni/Sn	4	
				1	HORIZONTL SHIELD	Cu ALLOY		PRE-TIN	3	
1-2339800-1	2339800-1 	A	A	4	VERTICAL SHIELD	Cu ALLOY	13.96	PRE-TIN	2	
				1	HOUSING	PA4T-GF30		WHITE	1	
				12	PIN	Cu ALLOY		Ni/Sn	4	
PN FOR PACKAGE IN TUBE	PN FOR PACKAGE IN TRAY	REV.	CODE	QTY.	DESCRIPTION	MATERIAL	WEIGHT (g)	COLOR/SURFACE	POS	
THIS DRAWING IS A CONTROLLED DOCUMENT.					DWN A HUANG 19SEP18		 TE Connectivity			
					CHK F-PAN 19SEP18					
					APV W.WU 19SEP18					
					NAME					
					PRODUCT SPEC					
					108-9A568		MATEnet 90deg HEADER 2X3 PORTS			
					APPLICATION SPEC					
					SIZE					
					CASE CODE					
					DRAWING NO					
MATERIAL					FINISH		WEIGHT		RESTRICTED TO	
- see table					- see table		A 1		- ©=2339800	
					RESTRICTED CUSTOMER		SCALE		SHEET	
							3:1		1 OF 1	
									REV A	