




RECOMMENDED PCB LAYOUT
FOR USE WITH 0.20[.008] THICK STENCIL

4	35.56 [1.400]	14	37.69 [1.484]	30	3-1977939-0
4	2.54 [0.100]	1	4.67 [0.184]	4	1977939-4
PLATING	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN KIRAN HOLAL CHK MIKE MILLER APVD MIKE MILLER	17AUG2013 17AUG2013 17AUG2013	 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	SURFACE MOUNT HEADER ASSEMBLY, MOD II, BREAKAWAY,VERTICAL, DOUBLE ROW, .100 X .100 C/L, .025 SQ.POST,30 Pd/Ni
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.13 [.005] 4 PLC ± - ANGLES ± -		PRODUCT SPEC	
MATERIAL		FINISH		APPLICATION SPEC	SIZE
		SEE TABLE		—	CAGE CODE
				WEIGHT	DRAWING NO
				—	A1 00779C=1977939
				CUSTOMER DRAWING	RESTRICTED TO
					—
					SCALE
					8:1
					SHEET
					1 OF 1
					REV
					C