


### Features

- Wide VCC Supply Range: 1.65V~5.5V
- Low Quiescent Current: 35uATypical
- Channel-to-Channel Cross-talk: -30dB Typical
- Insertion loss: -1dB@1GHz, -2dB @1.5GHz, -3dB@5.1GHz
- Power-off Truly Isolated and Off-Isolation: -25dB Typical
- Pin-to-Pin FSA646
- Small Packaging:  
CSP-36(WLCSP-36(2.4x2.4))

### Applications

- Tablets and Notebooks
- Multi-Camera and Displays
- 4G/5G Smart Phone
- Telecom Signal Switching
- Mobile and AI Device


### Functional Diagram



### General Description

The is a high performance four-data lane MIPI, D-PHY switch. This single-pole, double-throw (SPDT) switch is optimized for switching between two high-speed or low-power MIPI sources. The is has wide bandwidth and maintains good signal integrity, which makes it ideal is designed for the MIPI specification and allows connection to a CSI or DSI module. 36-Ball Wafer Level Chip Scale Package (WLCSP) 2.4mm x 2.4mm with Pb-free and Halogen-free, makes it ideal for mobile device.

### PIN CONFIGURATIONS



### PIN DESCRIPTION

| Pin # | Name  | Type | Description                                                              |
|-------|-------|------|--------------------------------------------------------------------------|
| A1    | VCC   | PWR  | 1.5~5V Positive Supply                                                   |
| A2    | GND   | GND  | Primary Ground Connection. Must be Connected to System Ground            |
| A3    | DA4N  | I/O  | A Side Data Path 4 Negative                                              |
| A4    | DA4P  | I/O  | A Side Data Path 4 Positive                                              |
| A5    | _OE   | I    | Chip Enable, Low Active                                                  |
| A6    | SEL   | I    | Channel Selection. When Low, A side selected; When High, B side selected |
| B1    | DB4N  | I/O  | B Side Data Path 4 Negative                                              |
| B2    | DB4P  | I/O  | B Side Data Path 4 Positive                                              |
| B3    | DA3N  | I/O  | A Side Data Path 3 Negative                                              |
| B4    | DA3P  | I/O  | A Side Data Path 3 Positive                                              |
| B5    | D4N   | I/O  | Common Side Data Path 4 Negative                                         |
| B6    | D4P   | I/O  | Common Side Data Path 4 Positive                                         |
| C1    | DB3N  | I/O  | B Side Data Path 3 Negative                                              |
| C2    | DB3P  | I/O  | B Side Data Path 3 Positive                                              |
| C3    | NC    | O    | Not Connected                                                            |
| C4    | NC    | O    | Not Connected                                                            |
| C5    | D3N   | I/O  | Common Side Data Path 3 Negative                                         |
| C6    | D3P   | I/O  | Common Side Data Path 3 Positive                                         |
| D1    | DB2N  | I/O  | B Side Data Path 2 Negative                                              |
| D2    | DB2P  | I/O  | B Side Data Path 2 Positive                                              |
| D3    | DA2N  | I/O  | A Side Data Path 2 Negative                                              |
| D4    | DA2P  | I/O  | A Side Data Path 2 Positive                                              |
| D5    | D2N   | I/O  | Common Side Data Path 2 Negative                                         |
| D6    | D2P   | I/O  | Common Side Data Path 2 Positive                                         |
| E1    | DB1N  | I/O  | B Side Data Path 1 Negative                                              |
| E2    | DB1P  | I/O  | B Side Data Path 1 Positive                                              |
| E3    | DA1N  | I/O  | A Side Data Path 1 Negative                                              |
| E4    | DA1P  | I/O  | A Side Data Path 1 Positive                                              |
| E5    | D1N   | I/O  | Common Side Data Path 1 Negative                                         |
| E6    | D1P   | I/O  | Common Side Data Path 1 Positive                                         |
| F1    | CLKBN | I/O  | B Side Clock Path Negative                                               |
| F2    | CLKBP | I/O  | B Side Clock Path Positive                                               |
| F3    | CLKAN | I/O  | A Side Clock Path Negative                                               |
| F4    | CLKAP | I/O  | A Side Clock Path Positive                                               |
| F5    | CLKN  | I/O  | Common Side Clock Path Negative                                          |
| F6    | CLKP  | I/O  | Common Side Clock Path Positive                                          |

### Absolute Maximum Ratings

(over operating free-air temperature range (unless otherwise noted) <sup>(1)</sup>)

|                                      |                  | Range      | Unit |
|--------------------------------------|------------------|------------|------|
| Power Supply Voltage                 | VCC              | -0.5 ~ 6.0 | V    |
| Control Pins                         | _OE, SEL         | -0.5 ~ VCC | V    |
| DC Switch I/O Voltage                | V <sub>SW</sub>  | -0.3 ~ VCC | V    |
| DC I/O Current                       | I <sub>IK</sub>  | -50 ~ 50   | mA   |
| Storage Temperature Range            | T <sub>STG</sub> | -55 ~ 150  | °C   |
| ESD HBM, ANSI/ESDA/JEDEC JS-001-2012 | VCC              | ±2         | kV   |
|                                      | _OE, SEL         | ±2         | kV   |
|                                      | Other I/O Pins   | ±2         | kV   |
| ESD MM, JESD22-A115                  | VCC              | ±200       | V    |
|                                      | _OE, SEL         | ±2         | kV   |
|                                      | Other I/O Pins   | ±2         | kV   |

(1) Stresses beyond those listed in Table-2 Absolute Maximum Ratings may cause permanent damage to the device. They are stress ratings only, which do not imply functional operation of the device at these or any other conditions. Beyond those indicated under Recommended Operating Conditions, exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

### Recommend operating ratings

|                       |                | Range      | Unit |
|-----------------------|----------------|------------|------|
| Power Supply Voltage  | VCC            | 1.65 ~ 5.5 | V    |
| Control Pins          | _OE, SEL       | 0 ~ VCC    | V    |
| Signal Pins           | HS Mode        | 0 ~ 0.3    | V    |
|                       | LP Mode        | 0 ~ 1.3    | V    |
| Operating Temperature | T <sub>A</sub> | -40 ~ 85   | °C   |

(1) If \_OE is left undriven, it will be pulled up to VCC by internal resistor; If SEL is left undriven, it will be pulled down to Ground by internal resistor.

### Electrical Characteristics (Ta=25°C, VCC=1.8V, unless otherwise specified)

| Parameter                                 | Symbol               | Conditions                                                                                                             | Min. | Typ. | Max. | Unit |
|-------------------------------------------|----------------------|------------------------------------------------------------------------------------------------------------------------|------|------|------|------|
| <b>Power Supply</b>                       |                      |                                                                                                                        |      |      |      |      |
| VCC Quiescent Current                     | I <sub>Q</sub>       | SEL=0 or VCC, _OE=0                                                                                                    | --   | 30   | --   | uA   |
| Power-down Current                        | I <sub>PD</sub>      | SEL=0 or VCC, _OE=VCC                                                                                                  | --   | --   | 1.0  | uA   |
| <b>DC Characteristics</b>                 |                      |                                                                                                                        |      |      |      |      |
| Input logic high                          | V <sub>IH</sub>      | VCC=1.8~4.5V                                                                                                           | 1.6  | --   | --   | V    |
| Input logic low                           | V <sub>IL</sub>      | VCC=1.8~4.5V                                                                                                           | --   | --   | 0.4  | V    |
| _OE Internal pull-up resistor             | R <sub>UP</sub>      |                                                                                                                        | --   | 2.0  | --   | MΩ   |
| SEL Internal pull-down resistor           | R <sub>DN</sub>      |                                                                                                                        | --   | 2.0  | --   | MΩ   |
| On-Resistance for LP MIPI                 | R <sub>ON_LP</sub>   | V <sub>IS</sub> = 1.2V I <sub>ON</sub> =8mA                                                                            | --   | 4.8  | 10   | Ω    |
| On-Resistance for HS MIPI                 | R <sub>ON_HS</sub>   | V <sub>IS</sub> = 0.2V I <sub>ON</sub> =8mA                                                                            | --   | 4.3  | 9.0  | Ω    |
| R <sub>ON</sub> Flatness for LP MIPI      | R <sub>FLAT_LP</sub> | V <sub>IS</sub> = 0 to 1.2V I <sub>ON</sub> =8mA                                                                       | --   | 0.9  | --   | Ω    |
| R <sub>ON</sub> Flatness for HS MIPI      | R <sub>FLAT_LP</sub> | V <sub>IS</sub> = 0 to 0.2V I <sub>ON</sub> =8mA                                                                       | --   | 0.2  | --   | Ω    |
| R <sub>ON</sub> Matching Between Channels | R <sub>MATCH</sub>   | V <sub>IS</sub> = 0 to 1.2V I <sub>ON</sub> =8mA                                                                       | --   | 0.1  | --   | Ω    |
| Switch Off Leakage Current                | I <sub>OFF</sub>     | _OE=VCC Dn, Dp =VCC<br>DAn, DBn, DAp, DBp=0 CLKn,<br>CLKp=0 CLKA <sub>n</sub> , CLKB <sub>n</sub> ,<br>CLKAp,CLKBp=VCC | -0.5 | --   | 0.5  | uA   |
| <b>AC Characteristics</b>                 |                      |                                                                                                                        |      |      |      |      |
| Enable Time _OE to Output                 | t <sub>EN</sub>      | R <sub>L</sub> =50Ω C <sub>L</sub> =0pF V <sub>IS</sub> = 0.6V                                                         | --   | 80   | 150  | uS   |
| Disable Time _OE to Output                | t <sub>DIS</sub>     | R <sub>L</sub> =50Ω C <sub>L</sub> =0pF V <sub>IS</sub> = 0.6V                                                         | --   | 40   | 250  | nS   |
| Turn-On Time SEL to Output                | t <sub>ON</sub>      | R <sub>L</sub> =50Ω C <sub>L</sub> =0pF V <sub>IS</sub> = 0.6V                                                         | --   | 400  | 1200 | nS   |
| Turn-Off Time SEL to Output               | t <sub>OFF</sub>     | R <sub>L</sub> =50Ω C <sub>L</sub> =0pF V <sub>IS</sub> = 0.6V                                                         | --   | 130  | 800  | nS   |

### Electrical Characteristics (Ta=25°C, VCC=1.8V, unless otherwise specified)


| Parameter                                               | Symbol      | Conditions                                          | Min. | Typ. | Max. | Unit |
|---------------------------------------------------------|-------------|-----------------------------------------------------|------|------|------|------|
| <b>AC Characteristics</b>                               |             |                                                     |      |      |      |      |
| Turn-Off Time SEL to Output                             | $t_{OFF}$   | $R_L=50\Omega$ $C_L=0pF$ $V_{IS}=0.6V$              | --   | 130  | 800  | nS   |
| Break-Before-Make Time                                  | $t_{BBM}$   | $R_L=50\Omega$ $C_L=0pF$ $V_{IS}=0.6V$              | --   | 250  | 500  | nS   |
| Propagation Delay                                       | $t_{PD}$    | $R_L=50\Omega$ $C_L=0pF$ $V_{IS}=0.6V$              | --   | 0.25 | --   | nS   |
| HS Mode Skew of Opposite Transitions of the Same Output | $t_{SK(P)}$ | $R_L=50\Omega$ $C_L=0pF$ $V_{IS}=0.3V$              | --   | 6.0  | --   | pS   |
| HS Mode Skew of Channel-to-Channel Single-Ended Skew    | $t_{SK(O)}$ | $R_L=50\Omega$ $C_L=0pF$ $V_{IS}=0.3V$              | --   | 6.0  | --   | pS   |
| Off Isolation                                           | Off         | $R_L = 50\Omega$ $f = 1.2GHz$<br>$V_{IS}=0.2V_{PP}$ | --   | -25  | --   | dB   |
| Crosstalk (Channel-to-Channel)                          | $X_{TALK}$  | $R_L = 50\Omega$ $f = 1.2GHz$<br>$V_{IS}=0.2V_{PP}$ | --   | -30  | --   | dB   |
| -3dB Bandwidth (Insertion Loss)                         | $BW_{-3dB}$ | $R_L=50\Omega$ $C_L=0pF$ Signal 0dBm                | --   | 5.1  | --   | GHz  |
| <b>Capacitance</b>                                      |             |                                                     |      |      |      |      |
| Switch On Capacitance                                   | $C_{ON}$    | $V_{Bias} = 0.2V$ , $f = 1250MHz$                   | --   | 1.5  | --   | pF   |
| Switch Off Capacitance                                  | $C_{OFF}$   | $V_{Bias} = 0.2V$ , $f = 1250MHz$                   | --   | 1.0  | --   | pF   |

**Note:**


- (1) Flatness is defined as the difference between maximum and minimum value of ON-resistance at the specified analog signal voltage points.
- (2) Crosstalk is inversely proportional to source impedance.

### Package information


CSP-36(WLCSP-36(2.4x2.4))



**Bottom-Up View**



**Top-Through View**



**Side View**

| Symbol | Dimensions In Millimeter |       |       |
|--------|--------------------------|-------|-------|
|        | Min.                     | Typ.  | Max.  |
| X      | 2.37                     | 2.40  | 2.43  |
| Y      | 2.37                     | 2.40  | 2.43  |
| X1     |                          | 0.16  |       |
| X2     |                          | 0.40  |       |
| X3     | 0.175                    | 0.205 | 0.235 |
| Y1     |                          | 0.16  |       |
| Y2     |                          | 0.40  |       |
| Z      | 0.550                    | 0.600 | 0.650 |
| Z1     | 0.145                    | 0.170 | 0.195 |
| Z2     | 0.340                    | 0.365 | 0.390 |
| Z3     | 0.395                    | 0.040 | 0.045 |