



Mallory Sonalert Products, Inc.

Sales Outline Drawing

Part #:

MSS5CH

Revision:

D

Specifications:

cUL Recognized to IEC60601-1-8 AMD1


Sound Level Category:	Loud	
Mode of Operation:	Cardiac Melody - High Priority	High Priority Alarm 10 beeps repeating every 2.5 seconds
Voltage Rating:	5 ± 0.5 VDC	
Loudness @ 10cm:	85 to 95 dB(A) Typ.	
Frequency:	150 to 4000 Hz	
Average Current Draw:	<200mA Typ.	
Ipk Current*:	400mA	
Housing Material:	Valox (UL94V-0), Color: Black	
Storage Temperature:	-30° to +60° C	
Operating Temperature:	-30° to +55° C	
Weight Typical:	6.0g	
Options:	Please contact factory.	

Dimensions: Inches (mm)

cUL Recognized

PATENT NUMBER: 7880593

ROHS Compliant



NOTE A:

TERMINALS - .031" DIA. NICKEL/TIN COATED BRASS.

NOTE B:

Mounting - Insert into printed circuit board and hand or machine solder. Units are suitable for wave soldering. Boards are not suitable for wash. Recommended maximum temperature and time duration for wave soldering is +270°C and 3 seconds respectively.

*Ipk = Instantaneous Peak