


used for:	D-SUB
-----------	-------



No. of pos.	A	B	C	Part NO.
9	31.2	25.0	38.3	165X02609X
15	39.3	33.3	40.5	165X02619X
25	53.4	47.0	47.8	165X02629X
37	69.9	63.5	52.2	165X02639X

⑥ TECHNICAL DATA:


1. BACKSHELL HALVES: ZINC DIE-CAST; NICKEL PLATED
2. ASSEMBLY SCREWS: STEEL; TIN PLATED
3. JACK SCREWS: STEEL; TIN PLATED + PA6
4. CABLE STRAIN RELIEF: PC
5. TEMPERATURE RANGE: -40°C to $+120^{\circ}\text{C}$
6. ATTENUATION FACTOR: $>40\text{dB}$ BETWEEN 30 MHz AND 1 GHz
7. ASSEMBLY INSTRUCTION SEE SHEET 2

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.

OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

				tolerance		 dim. in mm	
				2002	date	name	
				drawn	18.07.	Parei	
				appd.	18.07.	E. Mickenbecker	
				norm			
				d-old			
4 x b	Ä 4169	30.11.2011	Lehmen.				
a	Original						
rev.	description	date	name				

scale:	1:1
material:	SEE NOTES

title:	METAL HOOD 9-37pos. EMI/RFI SHIELDING with straight cable exit and jack screws
--------	--

dwg no:	DIN-A
	4
16K1A714	sh:1/2

part no:	SEE TABLE
----------	-----------

4

3

2



1

used for: D-SUB

ASSEMBLY INSTRUCTION:



Use two halves of strain relief
different sizes can be mixed

Strip cable 18mm and
shape cable to two pigtails





Attach the strain relief around the cable

Bend cable shielding back
on outside of strain relief




Mount connector and cable
into the backshell

Assemble the other half
screwing force: 100-120 Ncm.



THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

				tolerance		 dim. in mm
rev.	description	date	name			
				2011	date	name
				drawn	30.11.	Lehmenkühler
				appd.	30.11.	Fischer
				norm		
				d-old		
a	Original					

scale:	
material:	
title:	ASSEMBLY INSTRUCTION METAL HOOD 9-37pos. EMI/RFI SHIELDING with straight cable exit and jack screws
dwg no:	16K1A714
part no:	SEE SHEET 1

DIN-A
4
sh:2/2