

P	LTR	DESCRIPTION	DATE	DWN	APVD
	U	REDRAWN, RESIN SUPPLIER CHANGED	04 JUN2021	SB	KJK

D

D

C




C

B

B

A

A




2:1

PARTIAL SEC. Z-Z

- NOTES:
- 1 FINISH: 3-5 µm TIN OVER MIN 1.27 µm NICKEL
 - 2 FINISH: DUPLEX PLATED MIN. 0.38 µm GOLD IN CONTACT AREA AND 2.5 µm TIN IN SOLDER AREA, OVER MIN. 1.27 µm NICKEL.
 - 3 FINISH: DUPLEX PLATED MIN. 0.76 µm GOLD IN CONTACT AREA AND 2.5 µm TIN IN SOLDER AREA, OVER MIN. 1.27 µm NICKEL.
 - 4 MATERIALS:
 - HOUSINGS: FLAME RETARDANT THERMOPLASTIC, UL94V0, COLOR BLACK.
 - TIN AND GOLD PLATED CONTACTS: BRASS
 - 5 PN OBSOLETE

58.5	53.34	280388-3 5	280388-2	280388-1	22
48.3	43.18	281019-3 5	281019-2	281019-1 5	18
40.7	35.56	280387-3	280387-2	280387-1	15
33.1	27.94	280521-3 5	280521-2	280521-1	12
25.4	20.32	280509-3 5	280509-2	280509-1	9
22.9	17.78	280385-3	280385-2	280385-1	8
12.7	7.62	280384-3 5	280384-2	280384-1	4
D	B	3 PART NUMBER	2 PART NUMBER	1 PART NUMBER	NO. POS.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. CAMPIA	12FEB1990	 TE Connectivity		
DIMENSIONS: mm		CHK -	APVD -	NAME AMPMODU II SHROUDED HEADER DUAL ROW, STRAIGHT POST -		
	TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.3	PRODUCT SPEC 108-20025				
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±2°	APPLICATION SPEC -				
	MATERIAL 	WEIGHT -				
	FINISH - -		SIZE A3		CAGE CODE 00779	DRAWING NO C-280384
CUSTOMER DRAWING				SCALE 5:1	SHEET 1 OF 1	REV U