


LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			J	REVISED PER ECO-14-000068	26APR2014	NK	MM

- | | |
|---|---|
| 1 | ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS |
| 2 | TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD |
| 3 | THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING |
| 4 | POINT OF MEASUREMENT FOR PLATING THICKNESS |
| 5 | PARTS PACKAGED IN GPAX |
| 6 | OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI |



5 6 OBSOLETE	.284	.200	2	3	4-103239-2
	3.984	3.900	39	40	4-103239-0
	3.884	3.800	38	39	3-103239-9
	3.784	3.700	37	38	3-103239-8
	3.684	3.600	36	37	3-103239-7
	3.584	3.500	35	36	3-103239-6
	3.484	3.400	34	35	3-103239-5
	3.384	3.300	33	34	3-103239-4
	3.284	3.200	32	33	3-103239-3
	3.184	3.100	31	32	3-103239-2
	3.084	3.000	30	31	3-103239-1
	2.984	2.900	29	30	3-103239-0
	2.884	2.800	28	29	2-103239-9
	2.784	2.700	27	28	2-103239-8
	2.684	2.600	26	27	2-103239-7
	2.584	2.500	25	26	2-103239-6
	2.484	2.400	24	25	2-103239-5
	2.384	2.300	23	24	2-103239-4
	2.284	2.200	22	23	2-103239-3
	2.184	2.100	21	22	2-103239-2
2.084	2.000	20	21	2-103239-1	
OBSOLETE 6	1.984	1.900	19	20	2-103239-0
	1.884	1.800	18	19	1-103239-9
	1.784	1.700	17	18	1-103239-8
	1.684	1.600	16	17	1-103239-7
	1.584	1.500	15	16	1-103239-6
D BY 6-146281-3	1.484	1.400	14	15	1-103239-5
	1.384	1.300	13	14	1-103239-4
	1.284	1.200	12	13	1-103239-3
	1.184	1.100	11	12	1-103239-2
	1.084	1.000	10	11	1-103239-1
6 OBSOLETE	.984	.900	9	10	1-103239-0
	.884	.800	8	9	103239-9
	.784	.700	7	8	103239-8
	.684	.600	6	7	103239-7
	.584	.500	5	6	103239-6
	.484	.400	4	5	103239-5
	.384	.300	3	4	103239-4
	.284	.200	2	3	103239-3
	.184	.100	1	2	103239-2
	.084	—	—	1	103239-1
	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. NO.	H. MOLL	130C187	 TE Connectivity
		CHK.		200C787	
		APR'D.	T. CLARK	200C787	
DIMENSIONS:		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME	HEADER ASSY, MOD II, BREAKAWAY, SINGLE ROW, .100CL, VERTICAL, WITH .025 SQUARE POSTS
INCHES		0 FLC ± . 1 FLC ± . 2 FLC ± . 3 FLC ± .005 ANGLES ± .		PRODUCT SPEC	
		APPLICATION SPEC			
MATERIAL		FINISH		SIZE	
HOUSING: FLAME RETARDANT THERMOPLASTIC COLOR: BLACK POSTS: COPPER ALLOY		.00030 GOLD ON CONTACT AREA .00010-.00020 WHITE TIN LEAD ON SOLDER PAD, ALL OTHER .00000 NICKEL		DRAWING NO. A1 00779 C=103239	RESTRICTED TO
		WEIGHT		SCALE	
		RESTRICTED CUSTOMER		4:1 SHEET 1 of 1 REV. J	