


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION






ALL RIGHTS RESERVED.

© COPYRIGHT 2013 BY TE CONNECTIVITY.

LOC	DIST	REVISIONS				DATE	DWN	APVD
DW	—	P	LTR	DESCRIPTION				
		A2		ECR-12-012115		23OCT12	EL	WK




DETAIL W

TE LOGO &
DATE CODE

RECOMMENDED PCB LAYOUT (THICKNESS: 1.6mm)

(DIMENSION TOLERANCE: 1 PLC: ±0.1 2PLC: ±0.05)



W/O LED LIGHT

NOTE:

- MATERIAL:
HOUSING: THERMOPLASTIC HIGH TEMP., UL94 V-0, COLOR: BLACK.
CONTACT: PHOSPHOR BRONZE, THICKNESS: 0.35mm.
SHELL: BRASS, THICKNESS: 0.20mm.
LED LIGHT: EPOXY RESIN, THICKNESS: 0.50mm.
- FINISH:
CONTACT: GOLD PLATED (SEE TABLE) IN CONTACT AREA,
GOLD FLASH ON SOLDER TAILS,
50u" MIN. NICKEL UNDER PLATED ALL OVER.
SHELL: 20u" MIN. NICKEL PLATED.
LED LIGHT: 65u" MIN Ag PLATED
85u" MIN TIN PLATED.
- LED MUST BE REFLOW COMPATIBLE TO FOLLOWING
TEMPERATURE PROFILE (FOR 1 CYCLE): ABOVE 160°C FOR
120 SECONDS, PEAKING AT 245°C FOR 20~40 SECONDS.
- LED DEFECT RATE IS 6000 PPM MAX. AFTER IR REFLOW
PROCESS AS NOTE 3.
- WAVE SOLDER CAPABLE TO 265°C PER 109-202, CONDITION B.

△ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE	REEL	W/O	50μ"	3-1734719-8		
			30μ"	3-1734719-7		
			15μ"	3-1734719-6		
			6μ"	3-1734719-5		
		W/	50μ"	3-1734719-4		
			30μ"	3-1734719-3		
			15μ"	3-1734719-2		
			6μ"	3-1734719-1		
6 OBSOLETE	TRAY	W/O	50μ"	1734719-8		
			30μ"	1734719-7		
			15μ"	1734719-6		
			6μ"	1734719-5		
		W/	50μ"	1734719-4		
			30μ"	1734719-3		
			15μ"	1734719-2		
			6μ"	1734719-1		
OBSOLETE	OBSOLETE	OBSOLETE	PACKAGE	LED LIGHT	MIN. GOLD THICKNESS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	O. HU	13DEC2005
CHK	S. HOU	13DEC2005
APVD	W.J. KE	13DEC2005

PRODUCT SPEC

108-57535

APPLICATION SPEC

—

WEIGHT 3 GRAMS

CUSTOMER DRAWING

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

TE

TE Connectivity

MODULAR JACK, RJ45, SINGLE
ENTRY, DIP TYPE

A3

00779

C=1734719

SCALE

—

SHEET


1 OF 4

REV

A2

DIMENSIONS:

MM



MATERIAL


SEE NOTE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	± 0.5
1 PLC	± 0.3
2 PLC	± 0.2
3 PLC	± 0.1
4 PLC	± 0.1
ANGLES	± 3°






FINISH

SEE NOTE




DETAIL W

TE LOGO &
DATE CODE



RECOMMENDED PCB LAYOUT (THICKNESS: 1.6mm)
(DIMENSION TOLERANCE: 1 PLC: ±0.1 2PLC: ±0.05)



W/O LED LIGHT

NOTE:

- MATERIAL:
HOUSING: THERMOPLASTIC HIGH TEMP., UL94V-0, COLOR: BLACK.
CONTACT: PHOSPHOR BRONZE, THICKNESS: 0.35mm.
SHELL: BRASS, THICKNESS: 0.20mm.
- FINISH:
CONTACT: GOLD PLATED (SEE TABLE) IN CONTACT AREA,
GOLD FLASH ON SOLDER TAILS,
50u" MIN. NICKEL UNDER PLATED ALL OVER.
SHELL: 20u" MIN. NICKEL PLATED.
- WAVE SOLDER CAPABLE TO 265°C PER TYCO SPEC 109-202,
CONDITION B.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN —	TE Connectivity			
		CHK —				
DIMENSIONS: MM		APVD —	NAME			
		PRODUCT SPEC —	MODULAR JACK, RJ45, SINGLE ENTRY, DIP TYPE			
		APPLICATION SPEC —				
MATERIAL		WEIGHT —	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
SEE NOTE			A3	00779	C=1734719	—
FINISH		CUSTOMER DRAWING	SCALE	SHEET	REV	
SEE NOTE			—	2 of 4	A2	



TE Connectivity

MODULAR JACK, RJ45, SINGLE ENTRY, DIP TYPE

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-

© COPYRIGHT 2013 BY TE CONNECTIVITY.

ALL RIGHTS RESERVED.

LOC
DWDIST
—

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			

TOP TRAY

CLAPBOARD

INNER BOX

BOX

370mm(L)X255mm(W)X220mm(H)
11 TRAY/CARTON
TOTAL: 880 PCS
GROSS WEIGHT: 5Kg Ref.

TRAY

330mm(L)X225mm(W)X15mm(H)
80 PCS/TRAY

H

W

L

W

L

H

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	—
CHK	—
APVD	—
PRODUCT SPEC	—
APPLICATION SPEC	—
WEIGHT	—

TE

TE Connectivity

NAME			
MODULAR JACK, RJ45, SINGLE ENTRY, DIP TYPE			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C=1734719	—
CUSTOMER DRAWING		SCALE	SHEET
		—	3 of 4
		REV	A2

DIMENSIONS:

MM



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL

FINISH

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-

© COPYRIGHT 2013 BY TE CONNECTIVITY.

ALL RIGHTS RESERVED.

LOC
DWDIST
—

REVISIONS

P

LTR





DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1



NOTES:

- THE DIRECTION OF JACKS PUT INTO CARRIER.
- 10 EMPTY CAVITIES FOR BOTH OF TOP AND BOTTOM OF THE CARRIER.
- 200 PCS PRODUCTS BE PACKAGED ONE REEL.
- BOX SIZE: 345(L)X345(W)X315(H)
6 REEL/BOX
TOTAL: 1200 PCS

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

—

CHK

—

APVD

—

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

—

NAME

TE

TE Connectivity

MODULAR JACK, RJ45, SINGLE ENTRY, DIP TYPE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=

1734719

—

CUSTOMER DRAWING

SCALE

—

SHEET

4 of 4

REV

A2

DIMENSIONS:

MM

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -

FINISH

MATERIAL

