


ROHS Compliant





MAPX	MODIFICATION	DATE	DRAW	APPROVE

General tolerances(mm)														0.1/10 ±2°
0 ~ 3	>3 ~ 6	>6 ~ 10	>10 ~ 18	>18 ~ 30	>30 ~ 50	>50 ~ 80	>80 ~ 120	>120 ~ 180	>180 ~ 250	>250 ~ 315	>315 ~ 400	>400 ~ 500	>500	
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50	

UL Standard	B	C	D
Rated Voltage(V)/Current(A)	150/6	/	/
IEEC Standard			
Overvoltage Category/Pollution Degree	Ⅲ/3	Ⅲ/2	Ⅲ/2
Rated Voltage(V)/Current(A)	/	130/8	/
Withstanding Voltage(V/1min)	/	AC2000	/
Torque Tightening(N·m/Lb.in)	M1.6, 0.15/1.3		
Wire Range(rigid and flexible)(mm ² /AWG)	26~18/0.5~1.0		
Pitch(mm)/Poles	2.54/N=02~18P		
Stripping length(mm)	5~6		
Operating temperature(°C)	-40~+105		
Conform to RoHS	Yes		



PCB LAYOUT



4	Screw	Steel	M1.6/Zn Plated
3	Cage	Copper Alloy	M1.6/Ni plated
2	Housing	PA66	UL94V-0
1	Pin header	Copper alloy	Sn Plated
ITEM	NAME OF PART	MATERIAL	NOTES

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: DG308-2.54	
DECIMALS:	ANGLES:	PAR	DGL254-NP28V-MG361
		DWN	Lucas
		CHKD	Ethan
		APVD	Jacob
		SCALE:1:1	UNIT:MM
		CUSTOMER COPY	SIZE:A4
			SHEET:1F1
			REV:A