

PJD45P04-AU

40V P-Channel Enhancement Mode MOSFET

Voltage

-40 V

Current

-45 A

Features


- $R_{DS(ON)}$, $V_{GS}@-10V$, $I_D@-15A < 17m\Omega$
- $R_{DS(ON)}$, $V_{GS}@-4.5V$, $I_D@-10A < 25m\Omega$
- High switching speed
- Improved dv/dt capability
- Low Gate Charge
- Low reverse transfer capacitance
- AEC-Q101 qualified
- Lead free in compliance with EU RoHS 2.0
- Green molding compound as per IEC 61249 Standard

Mechanical Data

- Case : TO-252AA Package
- Terminals : Solderable per MIL-STD-750, Method 2026
- Approx. Weight : 0.0104 ounces, 0.297grams



TO-252AA



Maximum Ratings and Thermal Characteristics ($T_A=25^\circ\text{C}$ unless otherwise noted)

PARAMETER		SYMBOL	LIMIT	UNITS
Drain-Source Voltage		V_{DS}	-40	V
Gate-Source Voltage		V_{GS}	± 20	
Continuous Drain Current (Note 4)	$T_C=25^\circ\text{C}$	I_D	-45	A
	$T_C=100^\circ\text{C}$		-28	
Pulsed Drain Current (Note 1)	$T_C=25^\circ\text{C}$	I_{DM}	-135	
Power Dissipation	$T_C=25^\circ\text{C}$	P_D	63	W
	$T_C=100^\circ\text{C}$		25	
Continuous Drain Current (Note 4)	$T_A=25^\circ\text{C}$	I_D	-8.5	A
	$T_A=70^\circ\text{C}$		-7	
Power Dissipation	$T_A=25^\circ\text{C}$	P_D	2.0	W
	$T_A=70^\circ\text{C}$		1.3	
Operating Junction and Storage Temperature Range		T_J, T_{STG}	-55~150	$^\circ\text{C}$
Typical Thermal Resistance (Note 4,5)	Junction to Case	$R_{\theta JC}$	2.0	$^\circ\text{C/W}$
	Junction to Ambient	$R_{\theta JA}$	62.5	

- Limited only By Maximum Junction Temperature



PJD45P04-AU

Electrical Characteristics ($T_A=25^{\circ}\text{C}$ unless otherwise noted)

PARAMETER	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNITS
Static						
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} =0V, I _D =-250uA	-40	-	-	V
Gate Threshold Voltage	V _{GS(th)}	V _{DS} =V _{GS} , I _D =-250uA	-1	-1.6	-2.5	
Drain-Source On-State Resistance	R _{DS(on)}	V _{GS} =-10V, I _D =-15A	-	14	17	mΩ
		V _{GS} =-4.5V, I _D =-10A	-	20	25	
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =-40V, V _{GS} =0V	-	-	-1	uA
Gate-Source Leakage Current	I _{GSS}	V _{GS} =±20V, V _{DS} =0V	-	-	±100	nA
Dynamic (Note 6)						
Total Gate Charge	Q _g	V _{DS} =-32V, I _D =-10A, V _{GS} =-4.5V (Note 1,2)	-	19	-	nC
Gate-Source Charge	Q _{gs}		-	5.3	-	
Gate-Drain Charge	Q _{gd}		-	6.6	-	
Input Capacitance	C _{iss}	V _{DS} =-25V, V _{GS} =0V, f=1MHZ	-	2030	-	pF
Output Capacitance	C _{oss}		-	190	-	
Reverse Transfer Capacitance	C _{rss}		-	139	-	
Turn-On Delay Time	td _(on)	V _{DS} =-20V, I _D =-1A, V _{GS} =-10V, R _G =6Ω (Note 1,2)	-	8.6	-	ns
Turn-On Rise Time	t _r		-	9.6	-	
Turn-Off Delay Time	td _(off)		-	77	-	
Turn-Off Fall Time	t _f		-	39	-	
Drain-Source Diode						
Maximum Continuous Drain-Source Diode Forward Current	I _S	---	-	-	-45	A
Diode Forward Voltage	V _{SD}	I _S =-1A, V _{GS} =0V	-	-0.71	-1	V

NOTES :

1. Pulse width $\leq 300\mu s$, Duty cycle $\leq 2\%$.
2. Essentially independent of operating temperature typical characteristics.
3. Repetitive rating, pulse width limited by junction temperature $T_{J(MAX)}=150^{\circ}\text{C}$. Ratings are based on low frequency and duty cycles to keep initial $T_J=25^{\circ}\text{C}$.
4. The maximum current rating is package limited.
5. $R_{\theta JA}$ is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins. Mounted on a 1 inch² with 2oz.square pad of copper.
6. Guaranteed by design, not subject to production testing.

PJD45P04-AU

TYPICAL CHARACTERISTIC CURVES




Fig.1 On-Region Characteristics




Fig.2 Transfer Characteristics




Fig.3 On-Resistance vs. Drain Current




Fig.4 On-Resistance vs. Junction temperature




Fig.5 On-Resistance Variation with V_{GS}




Fig.6 Body Diode Characteristics

PJD45P04-AU

TYPICAL CHARACTERISTIC CURVES




Fig.7 Gate-Charge Characteristics




Fig.8 Breakdown Voltage Variation vs. Temperature




Fig.9 Threshold Voltage Variation with Temperature




Fig.10 Capacitance vs. Drain-Source Voltage




Fig.11 Maximum Safe Operating Area






Fig.12 Normalized Thermal Transient Impedance

PJD45P04-AU

Part No Packing Code Version

Part No Packing Code	Package Type	Packing Type	Marking	Version
PJD45P04-AU_L2_000A1	TO-252AA	3,000pcs / 13" reel	D45P04	Halogen free

Packaging Information & Mounting Pad Layout





PJD45P04-AU

Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from Panjit International Inc..
- Panjit International Inc. reserves the rights to make changes of the content herein the document anytime without notification. Please refer to our website for the latest document.
- Panjit International Inc. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Panjit International Inc. does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications. Panjit International Inc. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Panjit International Inc. for any damages resulting from such improper use or sale.
- Since Panjit uses lot number as the tracking base, please provide the lot number for tracking when complaining.